

### - Materials:

Steel version

Body : steel (class 5.8)

Pin: hardened steel

Stainless steel version

Body: stainless steel 303

Pin: Hardened stainless steel 420

Ring: Stainless steel 301

### - Finish: Steel version

Pin: hardened, ground and blackened

Stainless steel version


Pin : hardened , polished and ground




### Info.

- Index bolts are used whenever lateral movement needs to be blocked. Once released, another position can be set.

- The ring allows the unlocking action to be automated; by using pneumatic cylinder for example or some other remote control mechanism.



Typical application



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD4	L1	L2	L4	H	SW1	SW2	Fx30°	Spring strength			Price each 1 to 5
											F1 (N)	F2 (N)	Stock*	
<b>Steel, hardened steel pin</b>														
DIA8-4	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	9,69 €
DIA10-5	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	9,23 €
DIA12-6	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	10,25 €
DIA16-8	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	13,66 €
DIA20-10	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	19,45 €
<b>Stainless steel, hardened stainless steel pin</b>														
DIA8-4/SS	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	16,95 €
DIA10-5/SS	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	16,15 €
DIA12-6/SS	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	18,98 €
DIA16-8/SS	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	25,35 €
DIA20-10/SS	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	41,90 €


\*Depending on availability - Dimensions in mm

## Our other products



VTSM

Ball head screws  
Hygienic Design®,  
Stainless steel



PRF\_PSP\_PR

Dual purpose strip  
and cover for  
aluminium profile,  
Inserts into slot



HTD5M\_25

HTD Heavy duty  
timing pulley, HTD5  
Aluminium



GP

Spring loaded toggle  
latch, With padlock-  
holder



BSPM

Miniature ballscrew,  
Nut+rolled ballscrew



OP3\_14\_06

Reducing sleeve for  
OP indicators,  
Reduction socket



BLHB40\_

Right angled gearbox,  
bored shafts, up to  
10.3 Nm



BABFCFO

Ball pin socket,  
Mounting collar with a  
round flange



PTAF80-PAMF80

Articulated fixable  
foot with pressed  
base Ø80, Ø 80



IN1

Internal gear, Steel  
20NCD2



CHA1056\_U4

Screw-in hinge,  
Section 40X40



COA-COG

Surface mounting  
plate, Surface  
mounting plate for  
clevis

## Complementary products



SDA

Locking bolt support  
bracket, Mounting  
holes parallel to  
locating bolt



SDB

Locking bolt support  
bracket, Mounting  
holes at 90° to  
locating bolt



BIM

Indexing plunger mini,  
miniature



PITA

Locking bolt, with T  
handle