

## Steel 20NCD2


## Module 0.7

- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

### Option

- Alternative number of teeth, up to 231

Torque and power indication			
For 50 teeth at 1000 rpm			
	20NCD2	20NCD2	brass
	Z10CNF18.09	hardened	
Nm	0.60	3.200	0.326
kW	0.06	0.336	0.030



### DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						G	PG	G	PG
G0.7-15	15	10,50	11,90	11,90	5	0,009	0,006	30,99 €	On request
G0.7-18	18	12,60	14,00	12,00	5	0,011	0,008	33,42 €	
G0.7-20	20	14,00	15,40	12,00	5	0,012	0,009	34,13 €	
G0.7-24	24	16,80	18,20	12,00	5	0,015	0,012	35,50 €	
G0.7-26	26	18,20	19,60	12,00	5	0,017	0,014	36,29 €	
G0.7-28	28	19,60	21,00	12,00	5	0,019	0,016	36,77 €	
G0.7-30	30	21,00	22,40	12,00	5	0,021	0,018	37,37 €	
G0.7-35	35	24,50	25,90	16,00	6	0,031	0,025	37,68 €	
G0.7-40	40	28,00	29,40	16,00	6	0,038	0,031	38,11 €	
G0.7-42	42	29,40	30,80	16,00	6	0,040	0,034	38,32 €	
G0.7-48	48	33,60	35,00	16,00	6	0,050	0,044	39,05 €	
G0.7-50	50	35,00	36,40	16,00	6	0,053	0,047	39,47 €	
G0.7-60	60	42,00	43,40	16,00	6	0,073	0,067	41,17 €	
G0.7-70	70	49,00	50,40	16,00	8	0,094	0,092	42,88 €	
G0.7-76	76	53,20	54,60	16,00	8	0,109	0,107	45,16 €	
G0.7-175	175	122,50	123,90	25,00	12	0,566	0,547	119,63 €	
↓ Gears available up to this size									
G0.7-198	198	138,60	140,00	Dimensions: contact us					

\*Depending on availability - Dimensions in mm