

- Materials:

Steel version

Body : steel (class 5.8)

Pin: hardened steel

Stainless steel version

Body: stainless steel 303

Pin: Hardened stainless steel 420

Ring: Stainless steel 301

- Finish: Steel version

Pin: hardened, ground and blackened

Stainless steel version


Pin : hardened , polished and ground




Info.

- Index bolts are used whenever lateral movement needs to be blocked. Once released, another position can be set.

- The ring allows the unlocking action to be automated; by using pneumatic cylinder for example or some other remote control mechanism.



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD4	L1	L2	L4	H	SW1	SW2	F _{x30°}	Spring strength			Price each 1 to 5
											F1 (N)	F2 (N)	Stock*	
Steel, hardened steel pin														
DIA8-4	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	9,69 €
DIA10-5	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	9,23 €
DIA12-6	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	10,25 €
DIA16-8	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	13,66 €
DIA20-10	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	19,45 €
Stainless steel, hardened stainless steel pin														
DIA8-4/SS	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	16,95 €
DIA10-5/SS	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	16,15 €
DIA12-6/SS	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	18,98 €
DIA16-8/SS	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	25,35 €
DIA20-10/SS	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	41,90 €

*Depending on availability - Dimensions in mm

Our other products



ZG2

Plastic spur gear,
Machined plastic
(delrin)



VRM

Female swivelling
lifting rings, Female
swivelling




HK

Manual locking clamp,
Manual locking clamp
LRX



NIN

Self-locking nut, A2
Stainless steel



QNJ

Single row cylindrical
roller bearing, Single
flange on inner ring




GBS

Nut for ballscrew,
Flanged ballscrew nut



PSG1

Spur gear - precision
range, Case hardened
steel 20NCD2



M0

Worm and wheel set,
Machined plastic
(delrin)



AFA

Locking pin, with ring



RFK58B

Hypoid gearbox -
Stainless steel, up to
500 Nm



CNA-CNG

Right angled
mounting plate, Right
angled mounting



NKIA

Combined bearing
with inner ring, Axial
load in one direction

Complementary products



SDA

Locking bolt support
bracket, Mounting
holes parallel to
locating bolt



SDB

Locking bolt support
bracket, Mounting
holes at 90° to
locating bolt



PITAss

Locking bolt, with T
handle



PITAss

Locking bolt, with T
handle