


- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

Option

- Alternative number of teeth, up to 231



Torque and power indication			
For 50 teeth at 1000 rpm			
	20NCD2 Z10CNF18.09	20NCD2 hardened	brass fibre
Nm	1	5	0.54 0.450
kW	0.104	0.522	0.06 0.045



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Stock*	Price each 1 to 5	
						G	PG		G	PG
G0.7-9	9	7,00	8,40	8,40	4	0,004	0,003	-	22,05 €	22,05 €
G0.7-10	10	7,70	9,10	9,10	4	0,005	0,003	✓	22,05 €	22,05 €
G0.7-11	11	8,40	9,80	9,80	4	0,006	0,004	-	22,05 €	22,05 €
G0.7-12	12	8,40	9,80	9,80	5	0,006	0,005	-	22,05 €	22,05 €
G0.7-13	13	9,10	10,50	10,50	5	0,007	0,005	-	22,64 €	22,64 €
G0.7-15	15	10,50	11,90	11,90	5	0,009	0,006	✓	23,66 €	23,66 €
G0.7-18	18	12,60	14,00	12,00	5	0,011	0,008	-	25,51 €	25,51 €
G0.7-20	20	14,00	15,40	12,00	5	0,012	0,009	-	26,05 €	26,05 €
G0.7-24	24	16,80	18,20	12,00	5	0,015	0,012	-	27,10 €	27,10 €
G0.7-26	26	18,20	19,60	12,00	5	0,017	0,014	-	27,71 €	27,71 €
G0.7-28	28	19,60	21,00	12,00	5	0,019	0,016	-	28,07 €	28,07 €
G0.7-30	30	21,00	22,40	12,00	5	0,021	0,018	-	28,52 €	28,52 €
G0.7-35	35	24,50	25,90	16,00	6	0,031	0,025	-	28,77 €	28,77 €
G0.7-40	40	28,00	29,40	16,00	6	0,038	0,031	-	29,09 €	29,09 €
G0.7-42	42	29,40	30,80	16,00	6	0,040	0,034	-	29,25 €	29,25 €
G0.7-48	48	33,60	35,00	16,00	6	0,050	0,044	-	29,81 €	29,81 €
G0.7-50	50	35,00	36,40	16,00	6	0,053	0,047	✓	30,14 €	30,14 €
G0.7-60	60	42,00	43,40	16,00	6	0,073	0,067	-	31,43 €	31,43 €
G0.7-70	70	49,00	50,40	16,00	8	0,094	0,092	-	32,73 €	32,73 €
G0.7-76	76	53,20	54,60	16,00	8	0,109	0,107	-	34,47 €	34,47 €
G0.7-175	175	122,50	123,90	25,00	12	0,566	0,547	-	91,32 €	91,32 €

On request

Gears available up to this size

G0.7-198	198	138,60	140,00	Dimensions: contact us	On request
----------	-----	--------	--------	------------------------	------------


*Depending on availability - Dimensions in mm

Our other products



SUPCC

Self-centering
clamping hub steel,
With lock nut



GPLss

Brush, stainless steel



ACM_AZ

Mounting bracket for
bonnet fastener, Hook



PTMR

Telescopic furniture
foot, threaded stud



GPLbr

Brush, brass



GLB

Small 6 lobe female
handle,
Technopolymer -
Stainless steel



FR

Steel thread inserts,
Steel



PGM52-M4

Pull handle, Brass
Steel



CHT63

Asynchronous AC
motor 0.12 to 0.22kW,



BLHM30

Right angled gearbox,
double output shafts,



VRSF

Male swivelling lifting
ring, Male swivelling



NDS20

Double cross clamp,
Crossed

Complementary products



G0

Steel spur gear, Steel
20NCD2



G0

Steel spur gear, Steel
20NCD2