


## Module 1.75



- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

## Steel 20NCD2

Torque and power indication				
For 50 teeth at 1000 rpm				
	20NCD2	20NCD2		
	Z10CNF18.09	hardened	brass	fibre
Nm	16	75	8	6.40
kW	1.72	7.83	0.86	0.67



### DISCOUNTS

Qty	1+	6+	20+	40+
Disc. List	-12%	-25%	On request	

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						G	PG	G	PG
G1.75-9	9	17,50	21,00	21,00	10	0,047	0,022	23,14 €	On request
G1.75-10	10	19,25	22,75	22,75	10	0,059	0,029	23,14 €	
G1.75-11	11	21,00	24,50	24,50	10	0,073	0,037	23,14 €	
G1.75-12	12	21,00	24,50	24,50	10	0,073	0,037	23,14 €	
G1.75-13	13	22,75	26,25	25,00	10	0,083	0,045	23,74 €	
G1.75-14	14	24,50	28,00	25,00	10	0,092	0,054	25,04 €	
G1.75-15	15	26,25	29,75	25,00	10	0,102	0,064	26,17 €	
G1.75-16	16	28,00	31,50	25,00	12	0,104	0,069	26,64 €	
G1.75-17	17	29,75	33,25	25,00	12	0,115	0,080	27,35 €	
G1.75-18	18	31,50	35,00	25,00	12	0,126	0,092	28,53 €	
G1.75-19	19	33,25	36,75	25,00	12	0,139	0,104	29,68 €	
G1.75-20	20	35,00	38,50	30,00	12	0,171	0,117	31,68 €	
G1.75-21	21	36,75	40,25	30,00	12	0,185	0,131	32,42 €	
G1.75-22	22	38,50	42,00	30,00	12	0,199	0,145	32,93 €	
G1.75-23	23	40,25	43,75	30,00	12	0,214	0,160	34,63 €	
G1.75-24	24	42,00	45,50	30,00	12	0,230	0,175	36,16 €	
G1.75-25	25	43,75	47,25	30,00	12	0,246	0,191	36,41 €	
G1.75-26	26	45,50	49,00	30,00	12	0,263	0,208	36,65 €	
G1.75-27	27	47,25	50,75	30,00	12	0,280	0,226	37,29 €	
G1.75-28	28	49,00	52,50	40,00	15	0,335	0,235	37,40 €	
G1.75-29	29	50,75	54,25	40,00	15	0,353	0,254	37,82 €	
G1.75-30	30	52,50	56,00	40,00	15	0,373	0,274	38,87 €	
G1.75-31	31	54,25	57,75	40,00	15	0,393	0,294	39,72 €	
G1.75-32	32	56,00	59,50	40,00	15	0,414	0,315	40,09 €	
G1.75-33	33	57,75	61,25	40,00	15	0,436	0,336	40,31 €	

Dimensions in mm

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Weight (kg) G PG		Price each 1 to 5 G PG	
G1.75-34	34	59,50	63,00	40,00	15	0,458	0,359	40,96	€
G1.75-35	35	61,25	64,75	40,00	15	0,481	0,382	41,04	€
G1.75-36	36	63,00	66,50	50,00	15	0,569	0,405	42,43	€
G1.75-37	37	64,75	68,25	50,00	15	0,593	0,429	44,36	€
G1.75-38	38	66,50	70,00	50,00	15	0,618	0,454	45,36	€
G1.75-39	39	68,25	71,75	50,00	15	0,644	0,480	46,67	€
G1.75-40	40	70,00	73,50	50,00	15	0,670	0,506	47,69	€
G1.75-41	41	71,75	75,25	50,00	15	0,697	0,533	48,37	€
G1.75-42	42	73,50	77,00	50,00	15	0,724	0,560	49,44	€
G1.75-43	43	75,25	78,75	50,00	15	0,752	0,588	51,31	€
G1.75-44	44	77,00	80,50	50,00	15	0,781	0,617	52,01	€
G1.75-45	45	78,75	82,25	60,00	20	0,858	0,628	52,75	€
G1.75-46	46	80,50	84,00	60,00	20	0,889	0,658	53,79	€
G1.75-47	47	82,25	85,75	60,00	20	0,919	0,689	54,76	€
G1.75-48	48	84,00	87,50	60,00	20	0,951	0,720	56,20	€
G1.75-49	49	85,75	89,25	60,00	20	0,983	0,752	58,32	€
G1.75-50	50	87,50	91,00	60,00	20	1,016	0,785	58,98	€
G1.75-51	51	89,25	92,75	60,00	20	1,049	0,818	60,46	€
G1.75-52	52	91,00	94,50	60,00	20	1,083	0,853	61,96	€
G1.75-53	53	92,75	96,25	60,00	20	1,118	0,887	63,54	€
G1.75-54	54	94,50	98,00	80,00	20	1,356	0,923	68,58	€
G1.75-55	55	96,25	99,75	80,00	20	1,392	0,959	70,61	€
G1.75-56	56	98,00	101,50	80,00	20	1,428	0,996	73,64	€
G1.75-57	57	99,75	103,25	80,00	20	1,466	1,033	76,01	€
G1.75-58	58	101,50	105,00	80,00	20	1,504	1,071	78,35	€
G1.75-59	59	103,25	106,75	80,00	20	1,543	1,110	80,87	€
G1.75-60	60	105,00	108,50	80,00	20	1,582	1,149	84,14	€
G1.75-62	62	108,50	112,00	80,00	20	1,663	0,230	86,21	€
G1.75-64	64	112,00	115,50	80,00	20	1,746	1,314	88,74	€
G1.75-65	65	113,75	117,25	80,00	20	1,789	1,356	91,52	€
G1.75-66	66	115,50	119,00	80,00	20	1,833	1,400	94,34	€
G1.75-68	68	119,00	122,50	80,00	20	1,921	1,489	97,09	€
G1.75-70	70	122,50	126,00	100,00	20	2,272	1,580	99,75	€
G1.75-71	71	124,25	127,75	100,00	20	2,319	1,627	101,16	€
G1.75-72	72	126,00	129,50	100,00	20	2,367	1,674	103,05	€
G1.75-73	73	127,75	131,25	100,00	20	2,415	1,722	104,56	€
G1.75-74	74	129,50	133,00	100,00	20	2,463	1,771	106,13	€
G1.75-75	75	131,25	134,75	100,00	20	2,513	1,820	107,70	€
G1.75-76	76	133,00	136,50	100,00	20	2,563	1,870	109,26	€
G1.75-78	78	136,50	140,00	100,00	20	2,665	1,972	117,78	€
G1.75-80	80	140,00	143,50	100,00	20	2,769	2,077	124,72	€
G1.75-86	86	150,50	154,00	100,00	20	3,099	2,407	140,26	€
G1.75-90	90	157,50	161,00	100,00	20	3,333	2,640	153,55	€
G1.75-96	96	168,00	171,50	100,00	20	3,702	3,010	169,89	€
G1.75-98	98	171,50	175,00	100,00	20	3,831	3,139	176,75	€
G1.75-100	100	175,00	178,50	100,00	20	3,962	3,270	184,54	€
G1.75-105	105	183,75	187,25	100,00	20	4,302	3,609	On request	
G1.75-110	110	192,50	196,00	100,00	20	4,658	3,965	On request	
G1.75-115	115	201,25	204,75	100,00	20	5,031	4,338	On request	
G1.75-120	120	210,00	213,50	100,00	20	5,420	4,727	On request	

On request

↓ **Gears available up to this size** ↓

<b>G1.75-335</b>	<b>335</b>	<b>586,25</b>	<b>589,75</b>	<b>Dimensions: contact us</b>	<b>On request</b>
------------------	------------	---------------	---------------	-------------------------------	-------------------

*Dimensions in mm*

## Our other products



CHA60

Rectangular hinge, drilled or countersunk, Rectangular, drilled or C...



CLR

Straight clevis, Straight clevis for use with a male clevis



DOG316

Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm



FUSS

Bearing locknut, Self locking locknut - stainless steel lock washer



BOXdh

Boxed set of cylindrical dowel pins DIN6325, Boxed set - Solid DIN 6...



SH2

Parallel axis helical gear, Steel 20NCD2



ADL\_M

Male eye bolt conforms to DIN580, Stainless steel



DIV

Locking bolt, With grip - Steel



RESC

Retractable castor for aluminium profile, Retractable castor



G0

Steel spur gear, Steel 20NCD2



ZG0

Plastic spur gear, Machined plastic (delrin)



RFK48B

Hypoid gearbox - Stainless steel, up to 350 Nm

## Complementary products



YG1

HEAVY DUTY spur gear, Steel 35NCD6



G2

Steel spur gear, Steel 20NCD2