

- Materials:

Steel version

Body : steel (class 5.8)

Pin: hardened steel

Stainless steel version

Body: stainless steel 303

Pin: Hardened stainless steel 420

Ring: Stainless steel 301

- Finish: Steel version

Pin: hardened, ground and blackened

Stainless steel version


Pin : hardened , polished and ground




Info.

- Index bolts are used whenever lateral movement needs to be blocked. Once released, another position can be set.

- The ring allows the unlocking action to be automated; by using pneumatic cylinder for example or some other remote control mechanism.



Typical application



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD4	L1	L2	L4	H	SW1	SW2	Fx30°	Spring strength			Price each 1 to 5
											F1 (N)	F2 (N)	Stock*	
Steel, hardened steel pin														
DIA8-4	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	9,69 €
DIA10-5	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	9,23 €
DIA12-6	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	10,25 €
DIA16-8	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	13,66 €
DIA20-10	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	19,45 €
Stainless steel, hardened stainless steel pin														
DIA8-4/SS	4	M8x1,0	15	15	6	13	4	10	13	1,0	6	12	✓	16,95 €
DIA10-5/SS	5	M10x1,0	23	17	7	15	5	13	17	1,3	5	12	✓	16,15 €
DIA12-6/SS	6	M12x1,5	23	20	8	17	6	14	19	1,8	6	14	✓	18,98 €
DIA16-8/SS	8	M16x1,5	28	26	10	23	8	19	24	2,3	15	35	✓	25,35 €
DIA20-10/SS	10	M20x1,5	28	28	12	25	10	22	30	2,8	15	40	✓	41,90 €

*Depending on availability - Dimensions in mm

Our other products



SVG

Adjustable latch clamp with strike plate, Stroke from 106,7mm to 121...



Gdal

Double universal joint eco series, Low duty




PGT

Sliding profile, Sliding panel support



NPTF20

Spacer for tube carrier, Fixing accessory Ø10 to Ø14



T2

T type timing belt, T2.5 Steel cored polyurethane



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane



RCX-6

Spherical tilt washer - DIN6319, convex



SH1

Parallel axis helical gear, Steel 20NCD2



WS16

Drylin® W rail, Rail



SSB

Stainless steel bevel gear, 1:1



HW_HT

Half-rail guide, Rail



DBL880

Idler for slat top chain, Ranges 880 and 881

Complementary products



SDA

Locking bolt support bracket, Mounting holes parallel to locating bolt



SDB

Locking bolt support bracket, Mounting holes at 90° to locating bolt



PITAss

Locking bolt, with T handle



PITAss

Locking bolt, with T handle