

RGS Couplings for servo-motors

Torque: 0.5 to 190Nm


- No-wear elastic couplings
- No maintenance
- Low inertia and reduced size
- Easy blind assembly using standard screws
- Dampens vibration
- Electrically insulated

Definition

- TKN Nominal torque (Nm)
- TKMAX Max. torque (Nm)

Info

- Delivered not assembled



 **STANDARD BORE
IN STOCK**

DISCOUNTS

| Qty | 1+ | 5+ | 10+ | 25+ |
|------------|-----|------|------------|-----|
| Disc. List | -6% | -12% | On request | |

Transmissible torque (Nm) by friction for split hub

| Part number | Ø3 | Ø4 | Ø5 | Ø6 | Ø7 | Ø8 | Ø10 | Ø12 | Ø14 | Ø15 | Ø16 | Ø19 | Ø20 | Ø24 | Ø28 | Ø30 | Ø32 |
|-------------|----|------|------|------|------|------|-------|------|-------|------|------|------|------|------|-----|-----|-------|
| RGS-AL-5 | - | - | | | | | | | | | | | | | | | |
| RGS-AL-7 | | 0,65 | 0,70 | 0,74 | 0,79 | | | | | | | | | | | | |
| RGS-AL-9 | | 1,48 | - | 1,43 | - | 1,79 | 1,94 | | | | | | | | | | |
| RGS-AL-14 | | | 3,32 | 3,43 | - | 3,67 | 3,91 | 4,14 | 4,38 | | | | | | | | |
| RGS-AL-19 | | | | | | | 18,90 | - | 20,80 | 21,3 | 21,7 | - | 23,6 | | | | |
| RGS-AL-24 | | | | | | | | | | | | 27,5 | 28 | 29,0 | 31 | | |
| RGS-AL-28 | | | | | | | | | | | | | | 62,0 | 66 | 69 | 71 73 |

| Part number | Max. speed (rpm) | Torsional stiffness | | Radial stiffness (N/mm) | Torque (Nm) | | | Misalignment | | |
|-------------|------------------|---------------------|------------------|-------------------------|-------------|----------|------------|--------------|-------------|---------|
| | | static (Nm/rad) | dynamic (Nm/rad) | | T_{KSP} | T_{KN} | T_{KMAX} | axial (mm) | radial (mm) | angular |
| RGS-AL-5 | 38 000 | 5,16 | 16 | 154 | 0,08 | 0,50 | 1,00 | +0,4/-0,2 | 0,06 | 1° |
| RGS-AL-7 | 27 000 | 14,30 | 43 | 219 | 0,20 | 1,20 | 2,40 | +0,6/-0,3 | 0,10 | 1° |
| RGS-AL-9 | 19 000 | 31,50 | 95 | 262 | 0,45 | 3,00 | 6,00 | +0,8/-0,4 | 0,13 | 1° |
| RGS-AL-14 | 127 000 | 114,60 | 344 | 336 | 1,00 | 7,50 | 15,00 | +1/+0,5 | 0,15 | 1° |
| RGS-AL-19 | 9 550 | 1090,00 | 1720 | 1120 | 2,50 | 12,00 | 24,00 | +1,2/-0,5 | 0,10 | 1° |
| RGS-AL-24 | 6 950 | 2280,00 | 4010 | 1480 | - | 35,00 | 70,00 | +1,4/-0,5 | 0,14 | 1° |
| RGS-AL-28 | 5 850 | 4080,00 | 6754 | 1780 | - | 95,00 | 190,00 | +1,5/-0,7 | 0,15 | 1° |



Dimensions in mm

Characteristics

- Long-life
- Fixed by clamping jaw (except RGS-AL-5)
- Single-slit split hub (except RGS-AL-24 and RGS-AL-28 double slit)
- Preconstrained raised coupling
- Working temperature: -40°C to $+90^{\circ}\text{C}$ (occasional -50°C to $+120^{\circ}\text{C}$)
- Materials:
 - Hub: aluminium
 - Ring: polyurethane elastic (92 Shore A)

Uses

- Measuring and control instruments
- Servo-control, ball-screw systems
- Machine tools



DISCOUNTS

| Qty | 1+ | 5+ | 10+ | 25+ |
|-------|------|-----|------|------------|
| Disc. | List | -6% | -12% | On request |

| Part number | Clamping screw | | | Tightening torque T_A (Nm) |
|-------------|----------------|-------|---------------|------------------------------|
| | M_1 | t_1 | $\text{Ø}D_k$ | |
| RGS-AL-5 | M1,2 | 2,5 | 11,4 | - |
| RGS-AL-7 | M2,0 | 3,5 | 16,5 | 0,37 |
| RGS-AL-9 | M2,5 | 5,0 | 23,4 | 0,76 |
| RGS-AL-14 | M3,0 | 5,0 | 32,2 | 1,34 |
| RGS-AL-19 | M6,0 | 12,0 | 45,7 | 10,50 |
| RGS-AL-24 | M6,0 | 10,5 | 56,4 | 10,50 |
| RGS-AL-28 | M8,0 | 11,5 | 72,6 | 25,00 |

| Part number | Standard bore | | | | | | | | | Price each 1 to 4 |
|-------------|------------------------|-------|-------|----|-----------|----|----|-----|-----|-------------------|
| | $\text{Ø}A$ (H7) | D_n | d_n | L | $L_1:L_2$ | E | b | s | f | |
| RGS-AL-5 | Plain | 10 | - | 15 | 5 | 5 | 4 | 0,5 | 4,0 | 56,36 € |
| RGS-AL-7 | 4, 5, 6, 7 | 14 | - | 22 | 7 | 8 | 6 | 1,0 | 6,0 | 95,28 € |
| RGS-AL-9 | 4, 6, 8, 10 | 20 | 7,2 | 30 | 10 | 10 | 8 | 1,0 | 1,5 | 95,95 € |
| RGS-AL-14 | 5, 6, 8, 10, 12, 14 | 30 | 10,5 | 35 | 11 | 13 | 10 | 1,5 | 2,0 | 107,25 € |
| RGS-AL-19 | 10, 14, 15, 16, 20 | 40 | 18,0 | 66 | 25 | 16 | 12 | 2,0 | 3,0 | 235,93 € |
| RGS-AL-24 | 16, 19, 20, 24, 25 | 55 | 27,0 | 78 | 30 | 18 | 14 | 2,0 | 3,0 | 299,30 € |
| RGS-AL-28 | 20, 24, 25, 28, 30, 32 | 65 | 30,0 | 90 | 35 | 20 | 15 | 2,5 | 4,0 | 390,97 € |

Dimensions in mm



EKGS GERWAH Servo insert coupling

Torque range: 0.5 to 35 Nm

- Elastic backlash free coupling
- Reliable torque transmission
- Maintenance free
- Low inertia/size
- Easy to assembly, even in confined spaces
- Reduces vibration
- Materials:
 - Body: Aluminium
 - Spider: Polyurethane 92 Shore A (yellow)



Applications

- Metrology, control systems, driving, machine tools, driving lead screws

Torque (Nm) transmissible for hub secured using set screws

| Bore size | Ø3 | Ø4 | Ø5 | Ø6 | Ø7 | Ø8 | Ø9 | Ø10 | Ø11 | Ø12 | Ø13 | Ø14 | Ø15 | Ø16 | Ø17 | Ø18 | Ø20 | Ø22 | Ø24 | Ø28 |
|-----------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| EKGS-5 | 0,5 | 0,5 | 0,5 | | | | | | | | | | | | | | | | | |
| EKGS-7 | 1,2 | 1,2 | 1,2 | 1,2 | 1,2 | 1,2 | | | | | | | | | | | | | | |
| EKGS-9 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | 3 | | | | | | | | | | |
| EKGS-14 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | 7,5 | | | | | | | |
| EKGS-19 | | | | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 |
| EKGS-24 | | | | | | 20 | 22 | 24 | 26 | 29 | 31 | 34 | 35 | 35 | 35 | 35 | 35 | 35 | 35 | 35 |

| Part number | Transmissible nominal torque (Nm) | Tightened torque (Nm) | Max speed (rpm) | Moment of inertia (10^{-6} kgm ²) | axial (Nm) | Misalignment radial (Nm) | angular |
|-------------|-----------------------------------|-----------------------|-----------------|--|------------|--------------------------|---------|
| EKGS-5 | 0,5 | 1,3 | 47500 | 0,034 | -0,2/+0,4 | 0,06 | 1° |
| EKGS-7 | 1,2 | 1,3 | 34000 | 0,196 | -0,3/+0,6 | 0,10 | 1° |
| EKGS-9 | 3 | 3 | 24000 | 1,08 | -0,4/+0,8 | 0,13 | 1° |
| EKGS-14 | 7,5 | 6 | 16000 | 5,7 | -0,5/+1,0 | 0,15 | 1° |
| EKGS-19 | 10 | 6 | 12000 | 36 | -0,5/+1,2 | 0,10 | 1° |
| EKGS-24 | 35 | 6 | 8500 | 162 | -0,5/+1,4 | 0,14 | 1° |

Dimensions in mm



Characteristics


- Hardwearing
- Fixed using set screws
- Couplings are mounted pre-tensioned
- Shaft tolerance should be g6 or h7
- Contact surfaces should be free of grease

Bore

- Choose ØD1 and ØD2 from the ranges shown

Option

- Keyway according to DIN6885-1



DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 2+ | 4+ |
| Disc. | List | -6% | On request |

| Part number | L | ØA | E | ØD1/ ØD2 | | C | B | G | Weight (g) | Price each | |
|-------------|----|----|----|-----------|-------------|----|-----|------|------------|------------|-------------|
| | | | | No keyway | with keyway | | | | | No keyway | with keyway |
| EKGS-5 | 15 | 10 | 5 | 2-5 | - | 5 | 2,5 | 1xM3 | 5 | 41,88 € | - |
| EKGS-7 | 22 | 14 | 8 | 3-8 | 6-8 | 7 | 2,5 | 1xM3 | 9 | 43,39 € | 43,39 € |
| EKGS-9 | 30 | 20 | 10 | 3-12 | 6-10 | 10 | 5 | 2xM4 | 17 | 45,08 € | 45,08 € |
| EKGS-14 | 35 | 30 | 13 | 4-16 | 6-16 | 11 | 5 | 2xM6 | 41 | 56,69 € | 56,69 € |
| EKGS-19 | 66 | 40 | 16 | 6-24 | 6-24 | 25 | 10 | 2xM6 | 138 | 71,72 € | 71,72 € |
| EKGS-24 | 78 | 55 | 18 | 8-35 | 8-35 | 30 | 10 | 2xM6 | 282 | 89,99 € | 89,99 € |

Dimensions in mm

Backlash free coupling



DKGS GERWAH

Servo insert coupling
Torque range: 0.5 to 3 Nm

- Elastic backlash free coupling
- Reliable torque transmission
- Maintenance free
- Low inertia/size
- Easy to assemble, even in confined spaces
- Reduces vibration
- Materials:
 - Hub: Aluminium
 - Spider: Polyurethane 92 Shore A (yellow)

Applications

- Metrology, control systems, driving, machine tools, driving lead screws

Small size



Secured by a clamping hub

Torque (Nm) transmissible by friction for a split hub

| Bore size | Ø2 | Ø3 | Ø4 | Ø5 | Ø6 | Ø7 | Ø8 | Ø9 | Ø10 | Ø11 |
|-----------|-----|-----|-----|-----|-----|-----|----|----|-----|-----|
| DKGS-5 | 0,5 | 0,5 | 0,5 | - | - | - | - | - | - | - |
| DKGS-7 | - | 0,8 | 1,1 | 1,2 | 1,2 | 1,2 | - | - | - | - |
| DKGS-9 | - | 1,5 | 2 | 2,5 | 2,9 | 3 | 3 | 3 | 3 | 3 |

| Part number | Nominal torque (Nm) | Tightened torque (Nm) | Max speed (rpm) | Moment of inertia (10^{-6} kg.m ²) | axial (Nm) | Misalignment radial (Nm) | angular |
|-------------|---------------------|-----------------------|-----------------|---|------------|--------------------------|---------|
| DKGS-5 | 0,5 | 0,25 | 38000 | 0,034 | -0,2/+0,4 | 0,06 | 1° |
| DKGS-7 | 1,2 | 0,35 | 27000 | 0,196 | -0,3/+0,6 | 0,10 | 1° |
| DKGS-9 | 3 | 0,75 | 19000 | 1,08 | -0,4/+0,8 | 0,13 | 1° |

Dimensions in mm

Characteristics



- Hardwearing
- Secured by a clamping hub
- Couplings are mounted pre-tensioned
- Shaft tolerance should be g6 or h7
- Contact surfaces should be grease free

Bore

- Choose ØD1 and ØD2 from the ranges shown

Option

- Keyway according to DIN6885-1



DISCOUNTS

| Qty | 1+ | 2+ | 4+ |
|-------|------|-----|------------|
| Disc. | List | -6% | On request |

| Part number | L | ØA | K | ØH | E | ØD1/ ØD2 | | C | B | G | Weight (g) | Price each | |
|-------------|----|----|-----|------|----|-----------|-------------|----|-----|------|------------|------------|-------------|
| | | | | | | No keyway | with keyway | | | | | No keyway | with keyway |
| DKGS-5 | 15 | 10 | 3,2 | 11,5 | 5 | 2-4 | - | 5 | 2,5 | M1,6 | 5 | 45,31 € | - |
| DKGS-7 | 22 | 14 | 5 | 16,5 | 8 | 3-7 | 6-7 | 7 | 3,5 | M2 | 9 | 47,03 € | 47,03 € |
| DKGS-9 | 30 | 20 | 7,3 | 23,5 | 10 | 3-11 | 6-11 | 10 | 5 | M2,5 | 15 | 48,54 € | 48,54 € |

Dimensions in mm



BKGS **GERWAH**
BKGS2

Servo insert coupling
Torque range: 1.2 to 450 Nm

- Elastic backlash free coupling
- Reliable torque transmission
- Maintenance free
- Low inertia/size
- Easy to assemble, even in confined spaces
- Reduces vibration
- Materials:

Hub: Aluminium

Ring: Polyurethane 98 Shore A (Red)
except sizes 7 and 9 which are Shore
92 A (Yellow)



*With 1 or 2 tightening
screw depending on the size*

Applications

- Metrology, control systems, driving,
machine tools, driving lead screws

Torque (Nm) transmissible by friction for a split hub

| Bore size | Ø3 | Ø4 | Ø5 | Ø6 | Ø8 | Ø10 | Ø12 | Ø14 | Ø15 | Ø18 | Ø20 | Ø25 | Ø26 | Ø28 | Ø30 | Ø35 | Ø40 | Ø45 | Ø50 | Ø55 | Ø56 |
|-----------|-----|------|------|------|------|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| BKGS-7 | 0,7 | 0,9 | 1,1 | 1,2 | | | | | | | | | | | | | | | | | |
| BKGS-9 | 1,7 | 2,1 | 2,4 | 3,0 | 3,0 | | | | | | | | | | | | | | | | |
| BKGS2-12 | 3,5 | 4,3 | 5,1 | 6,8 | 8,4 | 9 | | | | | | | | | | | | | | | |
| BKGS2-14 | 8,4 | 10,2 | 12,5 | 12,5 | 12,5 | 12,5 | | | | | | | | | | | | | | | |
| BKGS2-19 | | | | | 17 | 17 | 17 | 17 | 17 | 17 | 17 | | | | | | | | | | |
| BKGS2-24 | | | | | 35 | 42 | 48 | 52 | 60 | 60 | 60 | 60 | 60 | 60 | | | | | | | |
| BKGS2-28 | | | | | | | | 96 | 102 | 121 | 133 | 160 | 160 | 160 | 160 | 160 | | | | | |
| BKGS2-38 | | | | | | | | 143 | 172 | 191 | 238 | 248 | 267 | 286 | 325 | 325 | 325 | | | | |
| BKGS2-42 | | | | | | | | | | | 221 | 277 | 288 | 310 | 332 | 387 | 443 | 450 | 450 | 450 | 450 |

| Part number | Transmissible torque (Nm) | Max. speed (rpm) | Moment of inertia (10 ⁻⁶ kg.m ²) | Misalignment | | | Tightening torque (Nm) |
|-------------|---------------------------|------------------|---|--------------|-------------|---------|------------------------|
| | | | | axial (mm) | radial (mm) | angular | |
| BKGS-7 | 1,2 | 27000 | 0,0001 | -0,3/+0,6 | 0,10 | 1° | 0,35 |
| BKGS-9 | 3 | 19000 | 0,0002 | -0,4/+0,8 | 0,13 | 1° | 0,75 |
| BKGS2-12 | 9 | 15000 | 0,00296 | +0,9/-0,4 | 0,08 | 0,9° | 2,1 |
| BKGS2-14 | 12,5 | 13000 | 0,006 | -0,5/+1,0 | 0,09 | 0,9° | 5 |
| BKGS2-19 | 17 | 10000 | 0,029 | -0,5/+1,2 | 0,06 | 0,9° | 10 |
| BKGS2-24 | 60 | 7000 | 0,121 | -0,5/+1,4 | 0,10 | 0,9° | 18 |
| BKGS2-28 | 160 | 6000 | 0,236 | -0,7/+1,5 | 0,11 | 0,9° | 43 |
| BKGS2-38 | 325 | 5000 | 0,797 | -0,7/+1,8 | 0,12 | 0,9° | 84 |
| BKGS2-42 | 450 | 4000 | 1,779 | -1,0/+2,0 | 0,14 | 0,9° | 84 |

Dimensions in mm

Characteristics



- Hardwearing
- Clamping hub
BKGS: clamp with 1 tightening screw
BKGS2: clamp with 2 tightening screws
- Coupling mounted under pre-tension
- Shafts must have g6 or h7 tolerance
- Degrease surfaces before assembly

Bore

- Choose ØD1 and ØD2 from within the range shown

Option

- Keyway according to DIN6885-1



DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 2+ | 4+ |
| Disc. | List | -6% | On request |

| Part number | L | ØD1/ØD2 | | With keyway | | | | Without keyway | | | | Price each | |
|-------------|-----|---------|----|-------------|-------|------|----|----------------|----------------|-------------|----------|------------|--|
| | | ØD1 | ØH | C1 | H3 | N | K | ØM | Without keyway | With keyway | | | |
| BKGS-7 | 20 | 14 | 17 | 3-7 | 6-7 | 6 | 8 | 3 | 5 | 1xM2 | 52,62 € | 52,62 € | |
| BKGS-9 | 26 | 19,5 | 23 | 4-11 | 6-11 | 8 | 10 | 4 | 7,5 | 1xM2,5 | 57,77 € | 57,77 € | |
| BKGS2-12 | 34 | 24,5 | 26 | 4-12 | 6-12 | 11 | 12 | 5 | 8,1 | 2xM3 | 79,22 € | 79,22 € | |
| BKGS2-14 | 32 | 29,5 | 33 | 5-15 | 6-15 | 9,5 | 13 | 5 | 10,5 | 2xM4 | 94,31 € | 94,31 € | |
| BKGS2-19 | 50 | 39,5 | 45 | 8-20 | 8-20 | 17 | 16 | 8 | 14 | 2xM6 | 112,76 € | 112,76 € | |
| BKGS2-24 | 58 | 54,5 | 57 | 10-32 | 10-32 | 18 | 18 | 7 | 20 | 2xM6 | 143,16 € | 143,16 € | |
| BKGS2-28 | 62 | 64,5 | 68 | 14-35 | 14-35 | 21 | 20 | 9 | 23,8 | 2xM8 | 191,15 € | 191,15 € | |
| BKGS2-38 | 85 | 79,5 | 86 | 15-45 | 15-45 | 26,5 | 23 | 13 | 29,5 | 2xM10 | 363,23 € | 363,23 € | |
| BKGS2-42 | 102 | 94,5 | 95 | 20-56 | 20-56 | 38 | 26 | 13,5 | 35 | 2xM10 | 677,35 € | 677,35 € | |

Dimensions in mm



ADSR **GERWAH** Servo insert coupling Torque range: 12.5 to 525 Nm

- Elastic backlash free coupling
- Reliable torque transmission
- Maintenance free
- Low inertia/size
- Easy to assemble, even in confined spaces
- Reduces vibration
- Materials:
 - Hub- Aluminium
 - Ring- Polyurethane 98 Shore A (Red)



Secured by a clamping hub

Applications

- Metrology, control systems, driving, machine tools, driving lead screws

Torque (Nm) transmissible by friction for a split hub

| Part number | Ø5 | Ø6 | Ø8 | Ø10 | Ø12 | Ø14 | Ø16 | Ø20 | Ø25 | Ø30 | Ø35 | Ø40 | Ø45 | Ø50 | Ø55 |
|-------------|-----|-----|-----|-----|-----|------|------|-----|-----|-----|-----|-----|-----|-----|-----|
| ADSR-14 | 4,8 | 6,0 | 7,7 | 9,4 | 11 | 12,5 | 12,5 | | | | | | | | |
| ADSR-19 | | 16 | 17 | 17 | 17 | 17 | 17 | | | | | | | | |
| ADSR-24 | | | | 37 | 43 | 50 | 56 | 60 | 60 | | | | | | |
| ADSR-28 | | | | 61 | 72 | 83 | 94 | 114 | 138 | 160 | 160 | | | | |
| ADSR-38 | | | | | 87 | 100 | 113 | 138 | 168 | 197 | 225 | 251 | 277 | | |
| ADSR-42 | | | | | | 174 | 197 | 242 | 296 | 348 | 398 | 450 | 450 | | |
| ADSR-48 | | | | | | | 276 | 343 | 424 | 502 | 525 | 525 | 525 | 525 | 525 |

| Part number | transmissible torque (Nm) | Tightened torque (Nm) | Max speed (rpm) | Moment of inertia 10 ⁻³ kg.m ² | axial (mm) | Misalignment radial (mm) | angular |
|-------------|---------------------------|-----------------------|-----------------|--|------------|--------------------------|---------|
| ADSR-14 | 12,5 | 2 | 13000 | 0,006 | -0,5/+1,0 | 0,09 | 0,9° |
| ADSR-19 | 17 | 11 | 10000 | 0,036 | -0,5/+1,2 | 0,06 | 0,9° |
| ADSR-24 | 60 | 15 | 7000 | 0,15 | -0,5/+1,4 | 0,10 | 0,9° |
| ADSR-28 | 160 | 32 | 6000 | 0,33 | -0,7/+1,5 | 0,11 | 0,9° |
| ADSR-38 | 325 | 38 | 5000 | 0,96 | -0,7/+1,8 | 0,12 | 0,9° |
| ADSR-42 | 450 | 84 | 4000 | 4,92 | -1,0/+2,0 | 0,14 | 0,9° |
| ADSR-48 | 525 | 145 | 3600 | 8,26 | -1,0/+2,1 | 0,16 | 0,9° |

Dimensions in mm

Characteristics



- Hardwearing
- Secured by a clamping hub
- Coupling mounted under pre-tension
- Shafts must have g6 or h7 tolerance
- Degrease surfaces before assembly

Bore

- Choose ØD1 and ØD2 from within the range shown

Option

- Keyway according to DIN6885-1



DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 2+ | 4+ |
| Disc. | List | -6% | On request |

| Part number | L | L1 | ØB | K | ØA | ØH | E | ØD1/ ØD2 | C | P | G | Price each | | |
|-------------|-----|----|----|------|-----|------|----|----------|----|------|-----|-------------|-----------|-------------|
| | | | | | | | | | | | | Weight (kg) | No keyway | with keyway |
| ADSR-14 | 35 | - | - | 11 | 30 | 32,2 | 13 | 5-16 | 11 | 5 | M3 | 0,042 | 72,81 € | 72,81 € |
| ADSR-19 | 66 | - | - | 14,5 | 40 | 46 | 16 | 6-20 | 25 | 12 | M6 | 0,158 | 103,52 € | 103,52 € |
| ADSR-24 | 78 | - | - | 20 | 55 | 57 | 18 | 10-32 | 30 | 10,5 | M6 | 0,304 | 121,12 € | 121,12 € |
| ADSR-28 | 90 | - | - | 24,5 | 65 | 71 | 20 | 10-38 | 35 | 11,5 | M8 | 0,505 | 156,77 € | 156,77 € |
| ADSR-38 | 114 | - | - | 30 | 80 | 83 | 24 | 12-48 | 45 | 15,5 | M8 | 0,934 | 242,25 € | 242,25 € |
| ADSR-42 | 126 | 28 | 85 | 32,5 | 95 | 91 | 26 | 14-54 | 50 | 18 | M10 | 3,8 | 828,38 € | 828,38 € |
| ADSR-48 | 140 | 32 | 95 | 37 | 105 | 106 | 28 | 15-60 | 56 | 21 | M12 | 4,9 | 968,65 € | 968,65 € |

Dimensions in mm