



# Spherical bushing **DIN 648**


Hard chrome/PTFE contact, with seals **GEET2RS**

- DIN 648, series E, ISO 6124/1
- Material: steel

## Advantages

- No maintenance

Maintenance free



## DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Ød	ØD	ØD1	S	C	α	Load capacity static (N)	dynamic (N)	Weight (g)	Stock*	Price each 1 to 5
GE17ET-2RS	17 <sup>+0.008</sup>	30 <sup>+0.008</sup>	25,0	14 <sup>+0.12</sup>	10 <sup>+0.24</sup>	10°	56000	22400	30	-	10,03 €
GE20ET-2RS	20 <sup>+0.010</sup>	35 <sup>+0.011</sup>	29,0	16 <sup>+0.12</sup>	12 <sup>+0.24</sup>	9°	78000	31500	60	✓	10,29 €
GE25ET-2RS	25 <sup>+0.010</sup>	42 <sup>+0.011</sup>	35,5	20 <sup>+0.12</sup>	16 <sup>+0.24</sup>	7°	127000	51000	110	-	12,76 €
GE30ET-2RS	30 <sup>+0.010</sup>	47 <sup>+0.011</sup>	40,7	22 <sup>+0.12</sup>	18 <sup>+0.24</sup>	6°	166000	65500	140	-	13,75 €
GE35ET-2RS	35 <sup>+0.012</sup>	55 <sup>+0.013</sup>	47,0	25 <sup>+0.12</sup>	20 <sup>+0.30</sup>	6°	224000	112000	220	✓	16,20 €
GE40ET-2RS	40 <sup>+0.012</sup>	62 <sup>+0.013</sup>	53,0	28 <sup>+0.12</sup>	22 <sup>+0.30</sup>	7°	280000	140000	300	-	18,67 €
GE45ET-2RS	45 <sup>+0.012</sup>	68 <sup>+0.013</sup>	60,0	32 <sup>+0.12</sup>	25 <sup>+0.30</sup>	7°	360000	180000	400	-	22,12 €
GE50ET-2RS	50 <sup>+0.012</sup>	75 <sup>+0.013</sup>	66,0	35 <sup>+0.12</sup>	28 <sup>+0.30</sup>	6°	440000	220000	540	-	27,04 €
GE60ET-2RS	60 <sup>+0.015</sup>	90 <sup>+0.015</sup>	80,0	44 <sup>+0.15</sup>	36 <sup>+0.40</sup>	6°	695000	345000	1000	-	43,75 €
GE70ET-2RS	70 <sup>+0.015</sup>	105 <sup>+0.015</sup>	92,0	49 <sup>+0.15</sup>	40 <sup>+0.40</sup>	6°	880000	440000	1500	-	58,52 €
GE80ET-2RS	80 <sup>+0.015</sup>	120 <sup>+0.015</sup>	105,0	55 <sup>+0.15</sup>	45 <sup>+0.40</sup>	6°	1140000	570000	2200	-	86,08 €
GE90ET-2RS	90 <sup>+0.020</sup>	130 <sup>+0.018</sup>	115,0	60 <sup>+0.20</sup>	50 <sup>+0.50</sup>	5°	1370000	695000	2700	-	112,15 €
GE100ET-2RS	100 <sup>+0.030</sup>	150 <sup>+0.018</sup>	130,0	70 <sup>+0.20</sup>	55 <sup>+0.50</sup>	7°	1730000	865000	4300	-	225,32 €
GE110ET-2RS	110 <sup>+0.030</sup>	160 <sup>+0.025</sup>	140,0	70 <sup>+0.20</sup>	55 <sup>+0.50</sup>	6°	1860000	930000	4700	-	282,90 €

\*Depending on availability - Dimensions in mm

## Our other products



VQT

Quarter-turn clamp lock, Plastic or stainless steel button



PLN

Cylindrical spacer, Thermoplastic



PCH

Knob for gripping, Mushroom



AZY

Cylindrical elastomount, Steel



RBntc

Swivel castor with central hole, Steel - rubber




DIA

Ring operated locking bolt, with ring



BHEX

Hexagonal cap, Black technopolymer



MLY

Bow shackle with eye bolt, Steel




G-ECO

Eco range Spur gear, Steel C45



PFL

P-FLEX Coupling, Set screw



T5\_11

T type timing pulley, T5 aluminium



BPM-Z

Plastic slotted spring plunger with ball tip, Plastic body + plastic...

## Complementary products



GE\_C

Spherical bushing, Hard chromium / PTFE



GE\_ES\_2RS

Spherical bushing, Steel / steel with seals