

Domino 120 adjustable slide



DOMI120

For C1 loads up to 1000 N



- Suitable for heavy loads
- Low coefficient of friction
- High quality slideways
- Low backlash system
- Very fine adjustment (0.05mm)
- Standard axis lengths
- Simple control system

Applications


- Fine adjustment of brazing/welding heads or plasma cutting heads
- Inkjet printer head positioning
- Camera positioning
- Machine parts positioning (milling head, milling spindles,...)
- Burner focusing
- Laser head positioning
- Moving stops
- Centred movement for lateral guidance (slide with left-right pin)



Options

- Other stroke lengths available, please contact us for details
- If a digital counter is required to be fitted to the linear slide, replace /XY by Z in the part number



DOMI120-CV Adjustable slide fitted with handwheel and counter





DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request


Part number	LA	LI	Stroke	Pitch (mm)	C1 (N)	C2 (N)	Maximum loads				Price each
							FA (N)	Mx (Nm)	My (Nm)	Mz (Nm)	
Slide only											
DOMI120-25	160	185	25	1	1000	700	300	15	20	12	771,12 €
DOMI120-50	160	210	50	1	1000	700	300	15	20	12	783,97 €
DOMI120-75	160	235	75	1	1000	700	300	15	20	12	798,96 €
DOMI120-100	160	260	100	1	1000	700	300	15	20	12	809,67 €
Slide with counter and handwheel											
DOMI120-25-CV/XY	160	185	25	1	1000	700	300	15	20	12	1 073,14 €
DOMI120-50-CV/XY	160	210	50	1	1000	700	300	15	20	12	1 036,98 €
DOMI120-75-CV/XY	160	235	75	1	1000	700	300	15	20	12	1 100,98 €
DOMI120-100-CV/XY	160	260	100	1	1000	700	300	15	20	12	1 133,83 €

Dimensions in mm



DOMI120 For Domino 120 adjustable slides

- **The fastening kit** is used to attach the DOMINO adjustable slide to its mounting surface.
- **The machineable mounting plate** allows you to attach other equipment to the adjustable slide.




Tool plate support



Clamping lever
DOMI120-LEVIER




Fastening set
DOMI120-B




Typical application




Mounting plate
DOMI120-M




Assembly angle bracket



Turntable DOMI 120-PT



DOMI120-B fastening set



DOMI120-M mounting plate

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Type	Price each
DOMI120-B	Fastening set	36,41 €
DOMI120-M	Mounting plate	130,66 €
DOMI120-LEVIER	Clamping lever	34,27 €
DOMI120-PT	Rotary turntable	563,34 €


Dimensions in mm



Connecting kits

For Domino 120 adjustable slides **DOMI120**

- **Connecting kits** are used to join two DOMINO adjustable slides.




Connecting kit
DOMI120-XY




Connecting kit DOMI120-XY




Connecting kit
DOMI 120-XZ




X-Y connecting kit



X-Z connecting kit



Typical application



Connecting kit
DOMI120-XZ

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Type	Price each
DOMI120-XY	Connecting kit X-Y	100,67 €
DOMI120-XZ	Connecting kit X-Z	128,52 €

Dimensions in mm

Our other products



CPAS-H
Folding bracket, For heavy loads



PRF_PL_4590
Joining plate for aluminium profile, Joint plate - 45x90 mm



BLH70
Right angled gearbox, from 26 to 128 Nm



HCSS
Set screw with hexagonal socket, Cup point



PCSS50SS
Chain sprocket - Stainless steel, 12.7mm (DIN 08B-1)



PR40
Articulated foot Ø50, Ø 50



TBE12
Economic mini-table with trapezoidal leadscrew, 2kg



PM3
Worm and wheel set, Non hardened steel



T5P_T10P
Connecting plate for T type timing belts, T10



PLM-20SC
Cylindrical magnet, Cylindrical magnet



TCL-ECL
Adjusting nut, Fine thread



VAP
Magnetic stud with central hole, With central hole

Complementary products



DOMI120
Accessories, Clamping lever



DOMI_MD
Domino rotary table, 55/1



DOMI120
Accessories, Fixing kit



DOMI120
Accessories, Plate