


Module 1.5

Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material: steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1.5-14	14	21,0	24,0	17	10	0,08-0,16	0,06	104,32 €
GG1.5-15	15	22,5	25,5	18	10	0,08-0,16	0,07	105,91 €
GG1.5-16	16	24,0	27,0	20	10	0,08-0,16	0,08	111,50 €
GG1.5-17	17	25,5	28,5	21	10	0,08-0,16	0,08	113,90 €
GG1.5-18	18	27,0	30,0	22	10	0,08-0,16	0,10	116,67 €
GG1.5-19	19	28,5	31,5	23	10	0,08-0,16	0,10	124,20 €
GG1.5-20	20	30,0	33,0	24	10	0,08-0,16	0,13	130,20 €
GG1.5-21	21	31,5	34,5	25	10	0,08-0,16	0,13	133,82 €
GG1.5-22	22	33,0	36,0	26	12	0,08-0,16	0,15	136,15 €
GG1.5-23	23	34,5	37,5	27	12	0,08-0,16	0,15	140,57 €

Dimensions in mm

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1.5-24	24	36,0	39,0	28	12	0,08-0,16	0,18	145,37 €
GG1.5-25	25	37,5	40,5	30	12	0,08-0,16	0,20	153,72 €
GG1.5-26	26	39,0	42,0	32	12	0,08-0,16	0,20	155,40 €
GG1.5-27	27	40,5	43,5	34	15	0,08-0,16	0,21	158,55 €
GG1.5-28	28	42,0	45,0	36	15	0,08-0,16	0,25	159,69 €
GG1.5-29	29	43,5	46,5	37	15	0,08-0,16	0,25	160,89 €
GG1.5-30	30	45,0	48,0	38	15	0,08-0,16	0,29	162,92 €
GG1.5-32	32	48,0	51,0	40	15	0,08-0,16	0,33	173,66 €
GG1.5-34	34	51,0	54,0	42	15	0,08-0,18	0,35	182,05 €
GG1.5-35	35	52,5	55,5	42	15	0,08-0,18	0,39	183,63 €
GG1.5-36	36	54,0	57,0	45	15	0,08-0,18	0,43	185,61 €
GG1.5-38	38	57,0	60,0	45	15	0,08-0,18	0,44	190,44 €
GG1.5-40	40	60,0	63,0	50	15	0,08-0,18	0,53	197,97 €
GG1.5-42	42	63,0	66,0	50	15	0,08-0,18	0,54	208,73 €
GG1.5-44	44	66,0	69,0	50	15	0,08-0,18	0,58	217,88 €
GG1.5-45	45	67,5	70,5	50	18	0,10-0,18	0,61	222,71 €
GG1.5-48	48	72,0	75,0	50	18	0,10-0,18	0,67	237,45 €
GG1.5-50	50	75,0	78,0	60	18	0,10-0,18	0,80	244,20 €
GG1.5-55	55	82,5	85,5	60	18	0,10-0,18	0,92	268,48 €
GG1.5-56	56	84,0	87,0	60	18	0,10-0,18	0,92	272,90 €
GG1.5-60	60	90,0	93,0	60	20	0,10-0,18	1,00	296,41 €
GG1.5-64	64	96,0	99,0	60	20	0,10-0,18	1,10	324,70 €
GG1.5-70	70	105,0	108,0	60	20	0,12-0,20	1,30	347,39 €
GG1.5-75	75	112,5	115,5	60	20	0,12-0,20	1,40	378,89 €
GG1.5-80	80	120,0	123,0	70	20	0,12-0,20	1,70	408,03 €
GG1.5-90	90	135,0	138,0	70	20	0,12-0,20	2,00	472,16 €
GG1.5-100	100	150,0	153,0	70	20	0,12-0,20	2,40	561,85 €

Dimensions in mm

Our other products



PRFRTR

Cross connector for aluminium profile, Cross connector




FB_ECO

Eco. range steel bevel gear, 4:1



PT881

Drive sprocket for slat top chain, Range 881



PRF-GUM

Aluminium profile anodising polisher, Polishing block




AT10courroie

AT type timing belt, AT10 Steel cored polyurethane




RFVbr

Stainless steel reaction arm, Reaction arm



RPP3

RPP heavy duty timing belt, RPP3



PO

Pull handle - Multi-sector, Smooth hole



CTZY

Diabolo shaped elastomount, Steel



HCSS

Set screw with hexagonal socket, Cup point



UGPC

Actuator guide kit, Short bearing



PSG25

Spur gear - precision range, Stainless steel 303

Complementary products