


## Module 1.5

Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material: steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1.5-14	14	21,0	24,0	17	10	0,08-0,16	0,06	104,32 €
GG1.5-15	15	22,5	25,5	18	10	0,08-0,16	0,07	105,91 €
GG1.5-16	16	24,0	27,0	20	10	0,08-0,16	0,08	111,50 €
GG1.5-17	17	25,5	28,5	21	10	0,08-0,16	0,08	113,90 €
GG1.5-18	18	27,0	30,0	22	10	0,08-0,16	0,10	116,67 €
GG1.5-19	19	28,5	31,5	23	10	0,08-0,16	0,10	124,20 €
GG1.5-20	20	30,0	33,0	24	10	0,08-0,16	0,13	130,20 €
GG1.5-21	21	31,5	34,5	25	10	0,08-0,16	0,13	133,82 €
GG1.5-22	22	33,0	36,0	26	12	0,08-0,16	0,15	136,15 €
GG1.5-23	23	34,5	37,5	27	12	0,08-0,16	0,15	140,57 €

Dimensions in mm

## DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1.5-24	24	36,0	39,0	28	12	0,08-0,16	0,18	145,37 €
GG1.5-25	25	37,5	40,5	30	12	0,08-0,16	0,20	153,72 €
GG1.5-26	26	39,0	42,0	32	12	0,08-0,16	0,20	155,40 €
GG1.5-27	27	40,5	43,5	34	15	0,08-0,16	0,21	158,55 €
GG1.5-28	28	42,0	45,0	36	15	0,08-0,16	0,25	159,69 €
GG1.5-29	29	43,5	46,5	37	15	0,08-0,16	0,25	160,89 €
GG1.5-30	30	45,0	48,0	38	15	0,08-0,16	0,29	162,92 €
GG1.5-32	32	48,0	51,0	40	15	0,08-0,16	0,33	173,66 €
GG1.5-34	34	51,0	54,0	42	15	0,08-0,18	0,35	182,05 €
GG1.5-35	35	52,5	55,5	42	15	0,08-0,18	0,39	183,63 €
GG1.5-36	36	54,0	57,0	45	15	0,08-0,18	0,43	185,61 €
GG1.5-38	38	57,0	60,0	45	15	0,08-0,18	0,44	190,44 €
GG1.5-40	40	60,0	63,0	50	15	0,08-0,18	0,53	197,97 €
GG1.5-42	42	63,0	66,0	50	15	0,08-0,18	0,54	208,73 €
GG1.5-44	44	66,0	69,0	50	15	0,08-0,18	0,58	217,88 €
GG1.5-45	45	67,5	70,5	50	18	0,10-0,18	0,61	222,71 €
GG1.5-48	48	72,0	75,0	50	18	0,10-0,18	0,67	237,45 €
GG1.5-50	50	75,0	78,0	60	18	0,10-0,18	0,80	244,20 €
GG1.5-55	55	82,5	85,5	60	18	0,10-0,18	0,92	268,48 €
GG1.5-56	56	84,0	87,0	60	18	0,10-0,18	0,92	272,90 €
GG1.5-60	60	90,0	93,0	60	20	0,10-0,18	1,00	296,41 €
GG1.5-64	64	96,0	99,0	60	20	0,10-0,18	1,10	324,70 €
GG1.5-70	70	105,0	108,0	60	20	0,12-0,20	1,30	347,39 €
GG1.5-75	75	112,5	115,5	60	20	0,12-0,20	1,40	378,89 €
GG1.5-80	80	120,0	123,0	70	20	0,12-0,20	1,70	408,03 €
GG1.5-90	90	135,0	138,0	70	20	0,12-0,20	2,00	472,16 €
GG1.5-100	100	150,0	153,0	70	20	0,12-0,20	2,40	561,85 €

Dimensions in mm

## Our other products




SLB  
Indexing plunger,  
steel class 5.8



HAS  
Captive C washer,  
Slotted flat headed  
shoulder screw



NAST  
Cam follower without  
axial guide, With  
interior ring



MF  
Shock Absorber  
-universal flange,  
Universal fixing



PGM52-M4  
Pull handle, Brass



CHMR40  
Worm and wheel gear  
reducer, up to 57 Nm



NDS20  
Double cross clamp,  
Crossed




RTTss  
Locking assembly,  
Medium/high torque



PM3  
Worm and wheel set,  
Non hardened steel



YG4  
HEAVY DUTY spur  
gear, Steel 35NCD6



RPP8  
RPP heavy duty  
timing belt, RPP8



TBbutee  
Axial thrust bearing,  
Steel balls

## Complementary products