



Module 1.0

Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material:
steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1-15	15	15	17	12	6	0,08-0,16	0,02	98,74 €
GG1-16	16	16	18	13	6	0,08-0,16	0,02	101,89 €
GG1-17	17	17	19	14	6	0,08-0,16	0,02	105,11 €
GG1-18	18	18	20	15	6	0,08-0,16	0,03	107,52 €
GG1-19	19	19	21	16	6	0,08-0,16	0,03	111,50 €
GG1-20	20	20	22	17	6	0,08-0,16	0,03	112,66 €
GG1-21	21	21	23	18	8	0,08-0,16	0,04	115,85 €
GG1-22	22	22	24	18	8	0,08-0,16	0,04	117,91 €
GG1-23	23	23	25	20	8	0,08-0,16	0,04	122,25 €
GG1-24	24	24	26	20	8	0,08-0,16	0,05	125,87 €

Dimensions in mm

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1-25	25	25	27	20	8	0,08-0,16	0,05	128,62 €
GG1-26	26	26	28	20	8	0,08-0,16	0,05	131,78 €
GG1-27	27	27	29	20	8	0,08-0,16	0,05	134,61 €
GG1-28	28	28	30	20	8	0,08-0,16	0,06	137,39 €
GG1-29	29	29	31	25	8	0,08-0,16	0,07	143,40 €
GG1-30	30	30	32	25	10	0,08-0,16	0,07	145,37 €
GG1-32	32	32	34	25	10	0,08-0,16	0,08	147,71 €
GG1-34	34	34	36	25	10	0,08-0,16	0,08	153,72 €
GG1-35	35	35	37	25	10	0,08-0,16	0,09	156,88 €
GG1-36	36	36	38	25	10	0,08-0,16	0,09	160,08 €
GG1-38	38	38	40	30	10	0,08-0,16	0,12	165,67 €
GG1-40	40	40	42	30	10	0,08-0,16	0,12	169,25 €
GG1-42	42	42	44	30	10	0,08-0,16	0,13	172,06 €
GG1-44	44	44	46	30	10	0,08-0,16	0,14	178,05 €
GG1-45	45	45	47	30	10	0,08-0,16	0,15	182,46 €
GG1-48	48	48	50	30	10	0,08-0,16	0,16	195,95 €
GG1-50	50	50	52	35	12	0,08-0,16	0,18	202,78 €
GG1-55	55	55	57	35	12	0,10-0,18	0,21	221,11 €
GG1-56	56	56	58	35	12	0,10-0,18	0,22	223,86 €
GG1-60	60	60	62	40	12	0,10-0,18	0,26	239,38 €
GG1-64	64	64	66	40	12	0,10-0,18	0,29	256,97 €
GG1-70	70	70	72	40	12	0,10-0,18	0,32	277,29 €
GG1-75	75	75	77	40	12	0,10-0,18	0,36	296,41 €
GG1-80	80	80	82	50	15	0,10-0,18	0,45	317,52 €
GG1-90	90	90	92	50	15	0,10-0,18	0,53	356,21 €
GG1-100	100	100	102	50	15	0,10-0,18	0,63	419,13 €
GG1-120	120	120	122	50	15	0,12-0,20	0,84	511,62 €

Dimensions in mm

Our other products



BOX-TOR-A

Box set of Nitrile O-rings in nitrile, 2.90 x 1.78mm to 28.17 x 3.53



BFM2

Flanged bronze nut, Bronze - 2 threads



PSG125

Spur gear - precision range, Pre-hardened Steel 35NCD6



AC

Strike for toggle latch, 12mm



CHAU

Screwed hinge, 270°



GLT3E-50

Telescopic drawer,




BPP

Pressed steel flanged bearing for light loads, Sheet steel



H1

Crossed helical gear crossed axis at 90°, Steel 20NCD2



T5M T10M

T type timing belt per metre, T10 Steel



UCP

Cast iron pillow block bearing, Cast iron



CHM50

Worm and wheel gear reducer, up to 107



CHT

Asynchronous AC Motor, 0.55 to 1.1kW

Complementary products