


Module 2.5

Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material: steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG2.5-14	14	35,0	40,0	28	15	0,10-0,20	0,28	135,45 €
GG2.5-15	15	37,5	42,5	30	15	0,10-0,20	0,33	141,42 €
GG2.5-16	16	40,0	45,0	32	15	0,10-0,20	0,38	151,70 €
GG2.5-17	17	42,5	47,5	35	15	0,10-0,20	0,36	156,51 €
GG2.5-18	18	45,0	50,0	38	15	0,10-0,20	0,50	165,28 €
GG2.5-19	19	47,5	52,5	39	15	0,10-0,20	0,46	172,44 €
GG2.5-20	20	50,0	55,0	40	18	0,10-0,20	0,55	184,81 €
GG2.5-21	21	52,5	57,5	42	18	0,12-0,22	0,54	189,21 €
GG2.5-22	22	55,0	60,0	44	18	0,12-0,22	0,60	199,55 €
GG2.5-23	23	57,5	62,5	46	18	0,12-0,22	0,66	205,12 €

Dimensions in mm

DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG2.5-24	24	60,0	65,0	48	18	0,12-0,22	0,81	215,48 €
GG2.5-25	25	62,5	67,5	50	20	0,12-0,22	0,93	222,71 €
GG2.5-26	26	65,0	70,0	54	20	0,12-0,22	0,87	235,09 €
GG2.5-27	27	67,5	72,5	56	20	0,12-0,22	0,94	240,25 €
GG2.5-28	28	70,0	75,0	60	20	0,12-0,22	1,20	251,01 €
GG2.5-29	29	72,5	77,5	60	20	0,12-0,22	1,10	258,17 €
GG2.5-30	30	75,0	80,0	65	20	0,12-0,22	1,30	270,50 €
GG2.5-32	32	80,0	85,0	70	20	0,12-0,22	1,50	286,51 €
GG2.5-34	34	85,0	90,0	70	20	0,12-0,22	1,60	306,00 €
GG2.5-35	35	87,5	92,5	70	20	0,12-0,22	1,70	310,78 €
GG2.5-36	36	90,0	95,0	70	20	0,12-0,22	1,80	328,67 €
GG2.5-38	38	95,0	100,0	70	20	0,12-0,22	1,80	350,99 €
GG2.5-40	40	100,0	105,0	70	25	0,14-0,24	2,10	365,74 €
GG2.5-42	42	105,0	110,0	75	25	0,14-0,24	2,20	390,50 €
GG2.5-44	44	110,0	115,0	75	25	0,14-0,24	2,30	402,78 €
GG2.5-45	45	112,5	117,5	75	25	0,14-0,24	2,60	409,60 €
GG2.5-48	48	120,0	125,0	75	25	0,14-0,24	2,80	441,08 €
GG2.5-50	50	125,0	130,0	80	25	0,14-0,24	3,10	467,81 €
GG2.5-55	55	137,5	142,5	80	25	0,14-0,24	3,50	513,64 €
GG2.5-56	56	140,0	145,0	80	25	0,14-0,24	3,60	526,34 €
GG2.5-60	60	150,0	155,0	80	25	0,14-0,24	4,20	579,75 €
GG2.5-70	70	175,0	180,0	80	25	0,14-0,24	5,30	724,47 €
GG2.5-75	75	187,5	192,5	90	25	0,14-0,24	6,20	797,02 €
GG2.5-80	80	200,0	205,0	90	25	0,14-0,24	6,90	890,61 €

Dimensions in mm


Our other products



SA_SAKH
Housing for linear bearing, Closed - light load



YG4
HEAVY DUTY spur gear, Steel 35NCD6



G1
Steel spur gear, Steel 20NCD2



RPP
Connecting plate for RPP type timing belts, RRP5



CQA20
Adjustment slide-system miniature, 20



ZG0
Plastic spur gear, Machined plastic (delrin)



LRRR
Latch with locking system, Aluminium



SDG_SS
Universal adjustable guide support bracket, Stainless steel



ACLEFS
Floor anchor for aluminium profile, Standard



H1
Crossed helical gear crossed axis at 90°, Steel 20NCD2



WSS
Symmetrical S shaped hook, Steel



CLSLCP_SS
Clevis components, short version, Stainless steel - short range

Complementary products