

Simple support base (bipod)



ESSBNV


Plastic

- **Bipod support base**
- Component for conveyor structure
- For round tube
- Materials
 - Body: reinforced polyamide
 - Screws: stainless steel 304



Accessories

- Add compatible **PR** feet to order (tome 5 p.169)



DISCOUNTS

Qty	1+	5+	10+
Disc. List	-5%	On request	

Part number	ØDF	Max. load resistance FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESSB-42/NV	42,4	15800	9600	0,612	43,57 €
ESSB-48/NV	48,3	15800	9600	0,612	43,57 €
ESSB-50/NV	50,8	15800	9600	0,612	43,57 €
ESSB-60/NV	60,3	15800	9600	0,752	43,57 €

Dimensions in mm


- **Combined bipod support part**
- Component for conveyor structure
- For round tube
- Materials
 - Body: reinforced polyamide
 - Screws: stainless steel 304

Accessories

- Add compatible PR feet to order (tome 5 p.169)



Typical application



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	ØDH	Max load resistance.FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESCB-42-42/NV	42,4	42,4	15800	9600	0,925	51,82 €
ESCB-48-42/NV	48,3	42,4	15800	9600	0,925	51,82 €
ESCB-48-48/NV	48,3	48,3	15800	9600	0,925	51,82 €
ESCB-50-42/NV	50,8	42,4	15800	9600	0,925	51,82 €
ESCB-50-48/NV	50,8	48,3	15800	9600	0,925	51,82 €
ESCB-60-42/NV	60,3	42,4	15800	9600	0,925	51,82 €
ESCB-60-48/NV	60,3	48,3	15800	9600	0,925	51,82 €

Dimensions in mm


- **High stability**
- Component for conveyor structure
- For round tube
- Materials:

Body: reinforced polyamide



Screws: stainless steel 304

Accessories

- Add compatible **PR** feet to order (tome 5 p.169)



Typical application



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	Max. load resistance FM (N)	Max. working load. FT (N)	Weight (kg)	Price each 1 to 4
ESST-42/NV	42,4	15800	9600	0,975	49,46 €
ESST-48/NV	48,3	15800	9600	0,975	49,46 €
ESST-50/NV	50,8	15800	9600	0,975	49,46 €
ESST-60/NV	60,3	15800	9600	0,975	49,46 €

Dimensions in mm

Our other products



WTM

Tightening washer -
DIN6340, Steel



EIM

Stainless steel U bolt,
Stainless steel




AC144

Strike for toggle latch,
22mm




PMB

Anti-vibration
machine mount, Oval
base plate



PSPE22

Conical flexible shaft
handle Ø22, Black
PVC



PRF_LIS

Door seal for
aluminium profile,
Black NBR



CQA20

Adjustment slide-
system miniature, 20



HTD5M_15

HTD Heavy duty
timing pulley, HTD5
Aluminium



PRF_GAL

Roller for aluminium
profile, Fixing kit for



Q1

Self-aligning radial
ball bearing, Steel



QTR

Tapered roller
bearing, Steel



PRF_GAL

Roller for aluminium
profile, Flat roller

Complementary products



ES

Support base (tripod),
Plastic



ES

Bipod support base,
Plastic



PR40

Articulated foot Ø40,
Ø 40



PR40

Articulated foot Ø50,
Ø 50