

# Steel telescopic drawer runners for groove mounting

## GLT2-17 Partial extension, load up to 10kg

- ***The course is shorter than the length of the rail***
- *Self-closing position*
- ***Load-bearing capacity per pair: 10kg (assembled vertically)***
- *The load-bearing capacities indicated refer to the maximum value for 20,000 cycles.*
- *Components:*
  *Plated steel drawer runners*
  *Plastic ball bearing cage*
  *Hardened steel ball bearings*








## Advantage

- *An economic solution for guiding drawers or other similar elements with low friction and high lateral stability*

## More info

- ***Sold by pair***
- *The load-bearing capacity of all telescopic drawer runners is tested according to the DIN EN 15338 standard, level 1.*




**DISCOUNTS**

| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |


| Part number | A | A2 | A3 | A3 | B | H | L | L1 | Stroke S | Groove depth T | Drawer depth from/to | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT2-17-104 | 37 | 32 | 132 | 10 | 10 | 17 | 164 | 182 | 104 | 6-7 | 185-260 | 4,84 € |
| GLT2-17-125 | 37 | 32 | 153 | 10 | 10 | 17 | 185 | 182 | 125 | 6-7 | 185-305 | 4,91 € |
| GLT2-17-145 | 37 | 32 | 185 | 10 | 10 | 17 | 217 | 214 | 145 | 6-7 | 220-355 | 5,13 € |
| GLT2-17-165 | 37 | 32 | 217 | 10 | 10 | 17 | 249 | 246 | 165 | 6-7 | 250-410 | 5,79 € |
| GLT2-17-348 | 37 | 32 | 418 | 10 | 10 | 17 | 450 | 278 | 348 | 6-7 | 450 | 6,80 € |
| GLT2-17-366 | 37 | 32 | 448 | 10 | 10 | 17 | 480 | 310 | 366 | 6-7 | 480 | 7,85 € |
| GLT2-17-368 | 37 | 32 | 468 | 10 | 10 | 17 | 500 | 310 | 368 | 6-7 | 500 | 8,14 € |
| GLT2-17-424 | 37 | 32 | 518 | 10 | 10 | 17 | 550 | 342 | 424 | 6-7 | 550 | 10,36 € |


*Dimensions in mm*

# Steel telescopic drawer runners for groove mounting

## Partial extension, load up to 12kg GLT2-27

- **The course is shorter than the length of the rail**
- Self-closing position
- **Load-bearing capacity per pair: 12kg (assembled vertically)**
- The load-bearing capacities indicated refer to the maximum value for 20,000 cycles.
- Components:
  Plated steel drawer runners
  Plastic ball bearing cage
  Hardened steel ball bearings







## Advantage

- An economic solution for guiding drawers or other similar elements with low friction and high lateral stability.

## More info

- **Sold by pair**
- The load-bearing capacity of all telescopic drawer runners is tested according to the DIN EN 15338 standard, level 1.




## DISCOUNTS

| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |

| Part number | A | A1 | A2 | A3 | B | H | L | L1 | Stroke S | Groove depth T | Drawer depth from/to | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT2-27-150 | 37 | 160 | 32 | 190 | 10 | 27 | 222 | 214 | 150 | 6-7 | 230-350 | 10,25 € |
| GLT2-27-232 | 37 | 288 | 32 | 296 | 10 | 27 | 328 | 342 | 232 | 6-7 | 350-550 | 15,77 € |


*Dimensions in mm*


# Telescopic steel slides with shock absorber

## GLT3-46A

### Integral extension, load up to 35kg

- ***The stroke is equal to the length of the rail***
- *Hold in closed position*
- *The drawer can be easily removed and separated from the guide rail by operating the release lever*
- *The damper cushions the telescopic slides as they close, automatically bringing them to the stop position*
- ***Lift per pair 35kg (vertically mounted)***
- *Lift per pair 35kg (vertically mounted)*
- *The load capacities indicated refer to the maximum value for 50,000 cycles*
- *Materials:*
  - *Zinc-plated and blue passivated steel slides*
  - *Steel and plastic ball cage*
  - *Hardened steel balls*







## Advantage


- *Cost-effective solution for guiding drawers or similar items with low friction and high lateral stability*


## More info

- ***Sold in pairs***
- *The load-bearing capacity of telescopic slides is tested to DIN EN 15338, level 2*



**With shock absorber**




## DISCOUNTS


| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |

| Part number | A | A1 | A2 | A3 | A5 | A6 | B | H | L | Stroke S | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT3-46A-300 | 35 | 128 | - | - | 35 | 171 | 12,7 | 46 | 300 | 300 | 39,35 € |
| GLT3-46A-350 | 35 | 128 | 64 | - | 35 | 220 | 12,7 | 46 | 350 | 350 | 43,25 € |
| GLT3-46A-400 | 35 | 128 | 64 | - | 35 | 254 | 12,7 | 46 | 400 | 400 | 47,20 € |
| GLT3-46A-450 | 35 | 128 | 96 | - | 35 | 294 | 12,7 | 46 | 450 | 450 | 51,16 € |
| GLT3-46A-500 | 35 | 128 | 96 | 64 | 35 | 344 | 12,7 | 46 | 500 | 500 | 55,05 € |
| GLT3-46A-550 | 35 | 128 | 96 | 128 | 35 | 394 | 12,7 | 46 | 550 | 550 | 59,96 € |
| GLT3-46A-600 | 35 | 128 | 96 | 160 | 35 | 444 | 12,7 | 46 | 600 | 600 | 64,91 € |


*Dimensions in mm*

# Full extension, load up to 45kg

# GLT3-46



- **The stroke is equal to the length of the rail**
- Hold in closed position
- The drawer can be easily removed and separated from the guide rail by operating the release lever.
- **Capacity per pair 45kg (vertically mounted)**
- The load capacities indicated refer to the maximum value for 20,000 cycles.
- Materials:
  Zinc-plated and blue passivated steel slides
  Steel and plastic ball cage
  Hardened steel balls






## Advantage

- An economic solution for guiding drawers or other similar elements with low friction and high lateral stability

## More info

- **Sold in pairs**
- The load-bearing capacity of telescopic slides is tested to DIN EN 15338, level 1




## DISCOUNTS

| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |

| Part number | A | A1 | A2 | A3 | A4 | A5 | A6 | A7 | B | H | L | Stroke S | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT3-46-300 | 35 | 128 | 96 | - | - | - | 35 | 242 | 12,7 | 46 | 300 | 300 | 20,50 € |
| GLT3-46-350 | 35 | 128 | 96 | - | - | - | 35 | 292 | 12,7 | 46 | 350 | 350 | 22,81 € |
| GLT3-46-400 | 35 | 128 | 96 | 96 | - | - | 35 | 342 | 12,7 | 46 | 400 | 400 | 24,97 € |
| GLT3-46-450 | 35 | 128 | 96 | 128 | - | - | 35 | 392 | 12,7 | 46 | 450 | 450 | 27,23 € |
| GLT3-46-500 | 35 | 128 | 96 | 128 | 64 | - | 35 | 442 | 12,7 | 46 | 500 | 500 | 28,99 € |
| GLT3-46-550 | 35 | 128 | 96 | 128 | 64 | 32 | 35 | 492 | 12,7 | 46 | 550 | 550 | 35,48 € |
| GLT3-46-600 | 35 | 128 | 96 | 128 | 96 | 32 | 35 | 542 | 12,7 | 46 | 600 | 600 | 40,18 € |
| GLT3-46-650 | 35 | 128 | 96 | 128 | 160 | 32 | 35 | 592 | 12,7 | 46 | 650 | 650 | 42,17 € |
| GLT3-46-700 | 35 | 128 | 96 | 128 | 192 | 32 | 35 | 642 | 12,7 | 46 | 700 | 700 | 45,31 € |


*Dimensions in mm*


# Steel telescopic slide

## GLT3E-50

### Super extension, load up to 60kg

- ***Stroke is greater than rail length for greater comfort and accessibility***
- *Hold in closed position*
- *The drawer can be easily removed and separated from the guide rail by operating the release lever*
- ***Capacity per pair 60kg (vertically mounted)***
- *The load capacities indicated refer to the maximum value for 20,000 cycles.*
- *Materials:*
  *Zinc-plated and blue passivated steel slides*
  *Steel and plastic ball cage*
  *Hardened steel balls*








## Advantage

- *Cost-effective solution for guiding drawers or similar items with low friction and high lateral stability*

## More info

- ***Sold in pairs***
- *The load-bearing capacity of telescopic slides is tested to DIN EN 15338, level 1*




## DISCOUNTS


| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |

| Part number | A | A1 | A2 | A3 | A4 | A5 | A6 | A7 | B | H | L | Stroke S | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT3E-50-338 | 35 | 128 | 96 | - | - | - | 35 | 242 | 12,7 | 50 | 300 | 338 | 45,27 € |
| GLT3E-50-388 | 35 | 128 | 96 | - | - | - | 35 | 292 | 12,7 | 50 | 350 | 388 | 49,37 € |
| GLT3E-50-438 | 35 | 128 | 96 | 96 | - | - | 35 | 342 | 12,7 | 50 | 400 | 438 | 53,85 € |
| GLT3E-50-488 | 35 | 128 | 96 | 128 | - | - | 35 | 392 | 12,7 | 50 | 450 | 488 | 58,34 € |
| GLT3E-50-538 | 35 | 128 | 96 | 128 | 64 | - | 35 | 442 | 12,7 | 50 | 500 | 538 | 62,82 € |
| GLT3E-50-588 | 35 | 128 | 96 | 128 | 64 | 32 | 35 | 492 | 12,7 | 50 | 550 | 588 | 68,45 € |
| GLT3E-50-638 | 35 | 128 | 96 | 128 | 96 | 32 | 35 | 542 | 12,7 | 50 | 600 | 638 | 74,07 € |
| GLT3E-50-688 | 35 | 128 | 96 | 128 | 160 | 32 | 35 | 592 | 12,7 | 50 | 650 | 688 | 79,64 € |
| GLT3E-50-738 | 35 | 128 | 96 | 128 | 192 | 32 | 35 | 642 | 12,7 | 50 | 700 | 738 | 86,39 € |


*Dimensions in mm*

## Super extension, load up to 90kg

# GLT3E-58



- ***Stroke is greater than rail length for greater comfort and accessibility***
- *Hold in closed position*
- *The drawer can be easily removed and separated from the guide rail by operating the release lever.*
- ***Capacity per pair 90kg (vertically mounted)***
- *The load capacities indicated refer to the maximum value for 20,000 cycles.*
- *Materials :*
  *Zinc-plated and blue passivated steel slides*
  *Steel and plastic ball cage*
  *Hardened steel balls*






## Advantage

- *Cost-effective solution for guiding drawers or similar items with low friction and high lateral stability*

## More info

- ***Sold in pairs***
- *Load capacity of telescopic slides H is tested to DIN EN 15338, level 1*




## DISCOUNTS

| Qty | 1+ | 4+ | 6+ |
|---|---|---|---|
| Disc. | Price | -10% | On request |

| Part number | A | A1 | A2 | A3 | A4 | A5 | B | H | L | Stroke S | Pair price 1 to 3 |
|---|---|---|---|---|---|---|---|---|---|---|---|
| GLT3E-58-338 | 31,75 | 57 | 122 | - | 31,75 | 233,5 | 19 | 58 | 300 | 338 | 57,91 € |
| GLT3E-58-388 | 31,75 | 57 | 172 | - | 31,75 | 283,5 | 19 | 58 | 350 | 388 | 63,70 € |
| GLT3E-58-438 | 31,75 | 57 | 111 | 111 | 31,75 | 333,5 | 19 | 58 | 400 | 438 | 69,48 € |
| GLT3E-58-488 | 31,75 | 57 | 136 | 136 | 31,75 | 383,5 | 19 | 58 | 450 | 488 | 75,29 € |
| GLT3E-58-538 | 31,75 | 57 | 161 | 161 | 31,75 | 433,5 | 19 | 58 | 500 | 538 | 85,43 € |
| GLT3E-58-588 | 31,75 | 57 | 186 | 186 | 31,75 | 483,5 | 19 | 58 | 550 | 588 | 88,33 € |
| GLT3E-58-638 | 31,75 | 57 | 211 | 211 | 31,75 | 533,5 | 19 | 58 | 600 | 638 | 95,53 € |
| GLT3E-58-688 | 31,75 | 57 | 236 | 236 | 31,75 | 583,5 | 19 | 58 | 650 | 688 | 102,78 € |
| GLT3E-58-738 | 31,75 | 57 | 261 | 261 | 31,75 | 633,5 | 19 | 58 | 700 | 738 | 111,47 € |

*Dimensions in mm*