

- **Indicator with an external sensor**
- Resolution: 0.1mm
- Max speed: 2.5m/s
- Display range: -99999 to 99999
- Display: LCD, character height 7.5mm
- Max distance between sensor and band: 1mm
- 3 button tactile keypad
- Sensor IP rating: IP57
- Indicator IP protection: IP54
- Working temperature: 0 to 50°C
- Relative humidity: 35-85%
- EMC protection: 2004/108/EC
- Power supply: ½AA 3.6B battery (Lithium-thionyl chloride)
- Battery life: Approx 4 years
- Material:

Sensor: Black anodised aluminium


Display housing: Plastic

NEW!



### Parameters

- Reset/preset, absolute/incremental, mm/inch/degrees, 3 origin points



### DISCOUNTS

Qty	1+	3+
Disc	List	On request

Part number	View	Length of sensor (mm)	Price each 1 to 2
F7-E-A-500	A	500	378,94 €
F7-E-A-1000	A	1000	378,94 €
F7-E-A-3000	A	3000	401,27 €
F7-E-A-5000	A	5000	423,60 €
F7-E-B-500	B	500	378,94 €
F7-E-B-1000	B	1000	378,94 €
F7-E-B-3000	B	3000	401,27 €
F7-E-B-5000	B	5000	423,60 €

Dimensions in mm

## Our other products



**BIMSS**  
Indexing plunger mini,  
miniature - Stainless  
steel




**BPP**  
Pressed steel flanged  
bearing for light  
loads, Sheet steel



**WTM**  
Tightening washer -  
DIN6340, Steel




**ESCON**  
Speed controller 5A, 5  
A



**RPPM**  
RPP type belt per  
metre, RPP14 Steel  
cored polyurethane



**ES**  
Bipod support base,  
Plastic



**BLHM30**  
Right angled gearbox,  
double output shafts,  
up to 4.4 Nm



**CHAPAM**  
Weld-on hinge with  
flat end, Steel



**BTC**  
End cap for square  
tube, Standard



**PARF110**  
Pressed steel base  
rigid foot, Swivelling  
Ø110



**PTMR**  
Telescopic furniture  
foot, threaded stud



**PTRSS**  
Idler chain sprocket,  
For hostile  
environments

## Complementary products



**F7-P-AM**  
Multifunction display,  
Magnetic band



**F7-P-AM**  
Multifunction display,  
Magnetic ring