

- **Indicator with an external sensor**
- Resolution: 0.1mm
- Max speed: 2.5m/s
- Display range: -99999 to 99999
- Display: LCD, character height 7.5mm
- Max distance between sensor and band: 1mm
- 3 button tactile keypad
- Sensor IP rating: IP57
- Indicator IP protection: IP54
- Working temperature: 0 to 50°C
- Relative humidity: 35-85%
- EMC protection: 2004/108/EC
- Power supply: ½AA 3.6B battery (Lithium-thionyl chloride)
- Battery life: Approx 4 years
- Material:

Sensor: Black anodised aluminium


Display housing: Plastic

NEW!



Parameters

- Reset/preset, absolute/incremental, mm/inch/degrees, 3 origin points



DISCOUNTS

Qty	1+	3+
Disc	List	On request


Part number	View	Length of sensor (mm)	Price each 1 to 2
F7-E-A-500	A	500	378,94 €
F7-E-A-1000	A	1000	378,94 €
F7-E-A-3000	A	3000	401,27 €
F7-E-A-5000	A	5000	423,60 €
F7-E-B-500	B	500	378,94 €
F7-E-B-1000	B	1000	378,94 €
F7-E-B-3000	B	3000	401,27 €
F7-E-B-5000	B	5000	423,60 €

Dimensions in mm

Our other products



RT25ss
Self-centering flanged locking assembly, Medium/high torque



H1
Crossed helical gear, crossed axis at 90°, Machined plastic (delrin)




BSM
Spring plunger with internal hexagonal socket, steel body and pin



BABam
Self-locking ball pin lifting ring for threaded hole, Self-locking



GDR880
Straight track for slat top chain, Ranges 880 and 881



T5courroie
T type timing belt, T5 Steel cored polyurethane



CLSCLP
Clevis components, short version, Steel - short range



RPCpl
Fixed castor with plate, Steel - Polyamide



PSG15
Spur gear - precision range, Case hardened



R204
Die spring ISO10243, Average



BPPL
Mini plain bearing ball transfer unit, For



AC156-157
Strike for toggle latch, 25.5mm

Complementary products



F7-P-AM
Multifunction display, Magnetic band



F7-P-AM
Multifunction display, Magnetic ring