

Thread inserts

FR_{TOOL}

Assembly tool



✓ INCREASED STOCK

DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Corresponding diameter D1	Stock*	Price each 1 to 9
FR-M5/TOOL	M5	✓	31,05 €
FR-M6/TOOL	M6	✓	32,08 €
FR-M8/TOOL	M8, M8x1	✓	33,46 €
FR-M10/TOOL	M10, M10x1,25	✓	35,86 €
FR-M12/TOOL	M12, M12x1,25	✓	38,74 €

*Depending on availability - Dimensions in mm

Our other products




VTHA
Magnetic screw with hexagonal head, Steel



CLM
Male clevis end, Stainless steel short



SCE_SS
Stainless steel U-shaped clamp, Stainless steel




EPRF
High helix leadscrew, Flanged nut - up to 40mm per rotation



RTN
BoWex® curved tooth gear coupling, Nylon




T39_T49
Extension spring in metre length steel, by the metre



GPLny
Brush, nylon



TCL-ECL
Adjusting nut, Fine thread



VP
Small 6 lobe threaded handle - male,



UFX
Uneflex® elastic coupling, range



SH3
Parallel axis helical gear, Machined plastic




WW20
Drylin® W slide, slide assembly

Complementary products



FR
Steel thread inserts, Steel



FRss
Stainless steel thread inserts, Stainless steel