

Thread inserts

FR_{TOOL}

Assembly tool



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Corresponding diameter D1	Stock*	Price each 1 to 9
FR-M5/TOOL	M5	✓	31,05 €
FR-M6/TOOL	M6	✓	32,08 €
FR-M8/TOOL	M8, M8x1	✓	33,46 €
FR-M10/TOOL	M10, M10x1,25	✓	35,86 €
FR-M12/TOOL	M12, M12x1,25	✓	38,74 €

*Depending on availability - Dimensions in mm

Our other products



D19_D29

Compression springs
in metre length steel,
by the metre



TBD

Manual leadscrew
table with opposing
threads, 40kg



BPM-Z

Plastic slotted spring
plunger with ball tip,
Plastic body + stainle...



RAS

90°ball and socket
joints DIN71802, Steel



CHTRP

Single and dual
output gearboxes, Up
to 9,1 Nm



PENV

Recessed handle,
screw fixing



BCM_T

Driving collar, Driving
collar



PPOss

Pad eye on mounting
plate oval, Stainless
steel



PM2

Worm and wheel set,
Machined plastic



SUPCC

Self-centering
clamping hub steel,



SB5_L

Chain link, Stainless
steel



ES


Support base (tripod),
Plastic

Complementary products



FR

Steel thread inserts,
Steel



FRss

Stainless steel thread
inserts, Stainless steel