



- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

Option

- Alternative number of teeth, up to 231



Torque and power indication			
For 50 teeth at 1000 rpm			
	20NCD2 Z10CNF18.09	20NCD2 hardened	brass fibre
Nm	1	5	0.54 0.450
kW	0.104	0.522	0.06 0.045



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Stock*	Price each 1 to 5	
						G	PG		G	PG
G0.7-9	9	7,00	8,40	8,40	4	0,004	0,003	-	22,05	€
G0.7-10	10	7,70	9,10	9,10	4	0,005	0,003	✓	22,05	€
G0.7-11	11	8,40	9,80	9,80	4	0,006	0,004	-	22,05	€
G0.7-12	12	8,40	9,80	9,80	5	0,006	0,005	-	22,05	€
G0.7-13	13	9,10	10,50	10,50	5	0,007	0,005	-	22,64	€
G0.7-15	15	10,50	11,90	11,90	5	0,009	0,006	✓	23,66	€
G0.7-18	18	12,60	14,00	12,00	5	0,011	0,008	-	25,51	€
G0.7-20	20	14,00	15,40	12,00	5	0,012	0,009	-	26,05	€
G0.7-24	24	16,80	18,20	12,00	5	0,015	0,012	-	27,10	€
G0.7-26	26	18,20	19,60	12,00	5	0,017	0,014	-	27,71	€
G0.7-28	28	19,60	21,00	12,00	5	0,019	0,016	-	28,07	€
G0.7-30	30	21,00	22,40	12,00	5	0,021	0,018	-	28,52	€
G0.7-35	35	24,50	25,90	16,00	6	0,031	0,025	-	28,77	€
G0.7-40	40	28,00	29,40	16,00	6	0,038	0,031	-	29,09	€
G0.7-42	42	29,40	30,80	16,00	6	0,040	0,034	-	29,25	€
G0.7-48	48	33,60	35,00	16,00	6	0,050	0,044	-	29,81	€
G0.7-50	50	35,00	36,40	16,00	6	0,053	0,047	✓	30,14	€
G0.7-60	60	42,00	43,40	16,00	6	0,073	0,067	-	31,43	€
G0.7-70	70	49,00	50,40	16,00	8	0,094	0,092	-	32,73	€
G0.7-76	76	53,20	54,60	16,00	8	0,109	0,107	-	34,47	€
G0.7-175	175	122,50	123,90	25,00	12	0,566	0,547	-	91,32	€

On request

Gears available up to this size

G0.7-198	198	138,60	140,00	Dimensions: contact us	On request
----------	-----	--------	--------	------------------------	------------

*Depending on availability - Dimensions in mm

Our other products



HW_HT

Half-rail guide, Rail




NPTF20

Fixed tube carrier,
Fixed Ø10 to Ø14



AC144

Strike for toggle latch,
22mm



H3

Crossed helical gear
crossed axis at 90°,
Machined plastic
(delrin)



G0

Steel spur gear, Steel
20NCD2



MFB_MHB

Moulded plastic bevel
gear (nylon), 4:1



EHD08-9

Internal epicyclic
servo reducers, from
35 to 50 Nm



PSG05S

Spur gear - precision
range, Stainless steel
303



PLM-C

Flat gripping magnet,
Flat holding magnet



GP

Spring loaded toggle
latch, Standard



E60B

Right angle helical
reducers, from 4.50 to
24 Nm



PTA50

Articulated levelling
foot, pressed base
Ø50, Ø 50

Complementary products



G0

Steel spur gear, Steel
20NCD2



G0

Steel spur gear, Steel
20NCD2