

Plastic



GAL21




- Load capacity: 100N static, 200N dynamic
- Turns on a double row of balls
- Colour: black
- Materials:
roller: black polypropylene
bearings: steel balls on hub

Info.

- Not sold individually, please contact us for details

Advantages

- Shock resistant
- Noiseless rotation



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Weight (g)	Stock*	Price each 1 to 49
GAL21-64	100	200	27	✓	2,37 €

*Depending on availability - Dimensions in mm

Our other products




Stainless steel bevel gear, 1:1




Chain sprocket with hardened teeth, 19.05mm (DIN12B-1)



Spoked handwheel with handle, Aluminium



RPP heavy duty timing belt, RPP5



RPP heavy duty timing belt, RPP14



Right angle helical reducers, from 3 to 41 Nm



Ground spur gear, Heat treated steel



Indexing plunger, steel class 5.8



Machined plastic bevel gear, 1:1



Technopolymer clamping lever - female, Plastic



Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



Stainless steel AC asynchronous motor 0.55 - 0.75kW, 0.55 to 0.75kW

Complementary products



Conveyor wheel, Zinc plated steel