

Self tapping inserts- coarse thread

INS100

For soft materials


- Self tapping insert with coarse external thread
- No collar
- Deforms on installation, no special tools required
- Hexagonal drive socket simplifies installation
- Chromed steel

Applications

- For use in rubber, soft plastic or soft wood

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L	Ød	SW	Recommended Ø drill		Packet qty	Weight (g)	Stock*	Price each by packet
					min	max				
INS100-M4/B	8,0	8	M4	4	6,6	6,9	20	1,4	✓	10,27 €
INS100-M5/B	10,0	10	M5	5	8,4	8,9	20	2,5	✓	13,06 €
INS100-M6/B	12,0	12	M6	6	10,0	10,4	20	4,8	✓	16,25 €
INS100-M8/B	14,0	15	M8	8	12,0	12,4	20	7,3	✓	27,27 €
INS100-M10/B	18,5	20	M10	10	16,2	16,7	15	19,2	✓	42,60 €
INS100-M12/B	22,0	30	M12	12	19,5	20,0	10	38,0	-	127,30 €

*Depending on availability - Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



RPP

Connecting plate for RPP type timing belts, RRP5



M

Bellows cover, Accessory:



PRF4590

Standard aluminium profile, 45 x 90 mm



NSK

Drylin® Rail end cap, Rail end cap



H3

Crossed helical gear crossed axis at 90°, Steel 20NCD2



RHTtcss

High Temperature Castor, up to 200kg



BLHB20

Right angled gearbox, bored shafts, up to 1.77 Nm



SSB

Stainless steel bevel gear, 1:1



HTD5M_15

HTD Heavy duty timing pulley, HTD5 Steel



DOMI80

Accessories, Plate



E60B

Right angle helical reducers, from 4.50 to 24 Nm



BLHM60

Right angled gearbox, double output shafts, up to 70 Nm

Complementary products



INS150

Self tapping insert with collar-coarse thread, With collar-coarse t...



INS

Self tapping steel insert, Steel



BOX-INS-W

Box set of self tapping inserts, Boxed set - For wood



INSTool

Insertion tool for self tapping inserts, Insertion tool