

Plastic



GAL21




- Load capacity: 100N static, 200N dynamic
- Turns on a double row of balls
- Colour: black
- Materials:
roller: black polypropylene
bearings: steel balls on hub

Info.

- Not sold individually, please contact us for details

Advantages

- Shock resistant
- Noiseless rotation



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Weight (g)	Stock*	Price each 1 to 49
GAL21-64	100	200	27	✓	2,37 €

*Depending on availability - Dimensions in mm

Our other products



PTA50

Articulated levelling foot, pressed base
Ø50, Ø 50



UCFL_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel



NTMbr

Set screw brass tip,
Brass-point



RDE-N

Sealing washer
Hygienic Usit®,
Stainless steel - Black
EPDM



AC156-157

Strike for toggle latch,
25.5mm



CNA-CNG

Right angled mounting plate, Right angled mounting plate for clevis



HSS

Shoulder screw
ISO7379, Hardened
Steel class 12.9




LVT

Miniature motorised
actuator 1A, 1 amper



NSR

Adjustable clamp,
Adjustable



SLS

Bearing block for
leadscrew, Fixed
Drylin® bearing block



BOXsap

Boxed set of spring
pins ISO8752, Boxed
set - Split ISO 8752



BAB

Hardened Stainless
steel ball pin,
Stainless steel
hardened

Complementary products



GAL22

Conveyor wheel, Zinc
plated steel