

Self tapping insert with collar-coarse thread

For soft materials

INS150

- Self tapping insert with coarse external thread
- With collar
- Deforms on installation, no special tools required
- Hexagonal drive socket simplifies installation
- Chromed steel

Applications



- For use in rubber, soft plastic or soft wood

Advantage

- Collar prevents insert being inserted too far

Info.

- Sold by the packet



DISCOUNTS

Qty	1+	10+	20+	30+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	L	Ød	SW	Recommended Ø drill		Packet qty	Weight (g)	Stock*	Price each by packet
					min	max				
INS150-M4/B	8,0	8	M4	4	6,6	6,9	20	1,4	✓	29,28 €
INS150-M5/B	10,0	12	M5	5	8,4	8,9	20	2,8	✓	36,42 €
INS150-M6/B	12,0	15	M6	6	10,0	10,4	20	6,0	✓	42,90 €
INS150-M8/B	14,0	18	M8	8	12,0	12,4	20	8,7	✓	71,53 €
INS150-M10/B	18,5	25	M10	10	16,2	16,7	15	24,2	✓	83,54 €
INS150-M12/B	22,0	25	M12	12	19,5	20,0	10	34,5	-	100,78 €

*Depending on availability - Dimensions in mm

Our other products



CLLCLLP
Clevis components,
long version, Steel -
long version



BOX-TOR-ORFS
Box set of Nitrile O-
rings NBR90Sh A, 7.65
x 1.78mm to 37.82 x
1.78



CQA20
Adjustment slide-
system miniature, 20



NSU
Universal 90° support
clamp, Universal 90°
support clamp



OP2
Mechanical digital
position indicator, 3
numbers




AT10-50ECO
AT type timing pulley,
Economy range -
AT10 aluminium



TPEpbd
Castor for aluminium
profile, Swivel with
brake



DER80
Stainless steel AC
asynchronous motor
0.55 - 0.75kW, 0.55 to
0.75kW



GPLso
Brush, silk



MET
Cylindrical sintered
bronze bush, Self-
lubricating sintered



VTHbr
Hexagonal headed
screw VTH - DIN933,
Brass



PPRss
Pad eye on mounting
plate round, Stainless
steel

Complementary products



INS100
Self tapping inserts-
coarse thread, Coarse
thread



BOX-INS-W
Box set of self tapping
inserts, Boxed set -
For wood



INSTool
Insertion tool for self
tapping inserts,
Insertion tool



CHC
Socket headed screw,
Steel class 12.19