

Plastic



GAL21




- Load capacity: 100N static, 200N dynamic
- Turns on a double row of balls
- Colour: black
- Materials:
roller: black polypropylene
bearings: steel balls on hub

Info.

- Not sold individually, please contact us for details

Advantages

- Shock resistant
- Noiseless rotation



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Weight (g)	Stock*	Price each 1 to 49
GAL21-64	100	200	27	✓	2,37 €

*Depending on availability - Dimensions in mm

Our other products



DOMI120

Accessories, Clamping lever




PPG

Indexing plunger with flange, With horizontal mounting flange



WJUM16

Drylin® W bearing block, Slide



PO

Pull handle - Multi-sector, Smooth hole



PRF_GAL

Roller for aluminium profile, Flat roller



SHS

Shoulder screw stainless steel 303, Stainless steel 303



BH02

Single housed bearing assembly, Bearing secured with circlips



BLHM70

Right angled gearbox, up to 128 Nm



LVT

Miniature motorised actuator 1A, 1 amper



PPF

Indexing plunger with flange, with drilled



HLC28

Right angle spiro bevel gearbox, Up to



CHALss

Piano hinge, Stainless steel

Complementary products



GAL22

Conveyor wheel, Zinc plated steel