

Plastic



GAL21




- Load capacity: 100N static, 200N dynamic
- Turns on a double row of balls
- Colour: black
- Materials:
roller: black polypropylene
bearings: steel balls on hub

Info.

- Not sold individually, please contact us for details

Advantages

- Shock resistant
- Noiseless rotation



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Static load (N)	Dynamic load (N)	Weight (g)	Stock*	Price each 1 to 49
GAL21-64	100	200	27	✓	2,37 €

*Depending on availability - Dimensions in mm

Our other products



GE

Toggle latches,
Miniature



SER

Magnetic doorstop for
aluminium profile,
Magnetic doorstop



PDD

Actuating plunger,
Non-rotating detector
shaft



CHMR30

Worm and wheel gear
reducer, up to 28 Nm



SHW

Plain washer, A2
Stainless steel



CQA20

Accessory for
adjustment slide-
system, 20




RFVbr

Stainless steel
reaction arm,
Reaction arm



MRASeco

Low cost stainless
steel quick link,
Stainless steel



RPPM

RPP type belt per
metre, RPP5 Steel



SSB

Stainless steel bevel
gear, 1:1



CHA1056-UPA

Molded polyamide
face-mounted hinge,



BPM

Slotted spring plunger
with ball tip, Steel

Complementary products



GAL22

Conveyor wheel, Zinc
plated steel