

Omni-directional roller

To be fitted to a Ø8mm axle




- Multiple rollers mounted on one axle work as a conventional roller with two possible directions of movement
- The "Snap in" function allows you to securely and quickly position two omnidirectional rollers together, and augrantees an optimised assembly
- Corrosion-resistant
- Suitable for dusty environments
- No maintenance required
- Materials:

technopolymer and stainless steel

- Control posts
- Assembly or handling stations

- Not sold individually, please contact us for details







Typical application

Allows the load to be moved in any direction

DISCOUNTS

Qty	1+	50+	100+	300+		
Disc.	List	-20%	-30%	On request		

Part numb	oer ø	D	х		Υ		w	٧	Max. load (daN)	Stock*	Price each 1 to 99
GAL48-C	OMNI 4	18	3	3		3	21,5	40	5	V	8,14 €
4.00			D /		-						

^{*}Depending on avaibility - Dimensions in mm



Our other products



Lip seal for panel, Door seal - Ø 4mm



Cross connector for aluminium profile, Cross connector



Parallel axis helical gear, Steel 20NCD2



Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



Stainless steel diabolo shaped elasto mount, Stainless steel



AT type timing belt, AT10 Steel cored polyurethane



Drylin® Linear table, Maintenance free



Miniature cam follower, Miniature



AT type timing belt, AT5 Steel cored polyurethane



Machined plastic bevel gear , 1:1



Bellows coupling Gerwah®, from 22 to 600Nm



Stainless steel diabolo shaped elasto mount, Stainless steel

Complementary products



Free running conveyor roller, PVC



Free roller, Steel