

To be fitted to a Ø8mm axle



GAL48

- Multiple rollers mounted on one axle work as a conventional roller with two possible directions of movement
- The "Snap in" function allows you to securely and quickly position two omni-directional rollers together, and guarantees an optimised assembly
- Corrosion-resistant
- Suitable for dusty environments
- No maintenance required
- Materials: technopolymer and stainless steel





Uses

- Control posts
- Assembly or handling stations

Info.

- Not sold individually, please contact us for details



Typical application

Allows the load to be moved in any direction

DISCOUNTS

Qty	1+	50+	100+	300+
Disc.	List	-20%	-30%	On request

Part number	ØD	X	Y	W	V	Max. load (daN)	Stock*	Price each 1 to 99
GAL48-OMNI	48	3	3	21,5	40	5	✓	8,14 €

*Depending on availability - Dimensions in mm

Our other products



PSG125

Spur gear - precision range, Case hardened steel 20NCD2




CMM

Male rod ends DIN ISO12240-4, Steel / bronze



PO

Pull handle - Multi-sector, Tapped recessed insert



SBF

Open flange bearing unit for food industry, cover



AKD

Bellows coupling Gerwah®, from 22 to 600Nm



VHEH

Hexagonal headed screw with collar Hygienic Usit®, Stainless steel



PTRSS

Idle chain sprocket, For hostile environments



KBS_UU

Stainless steel closed precision linear bearing, Precision - stainle...



GPB

Threaded spherical knob, With brass insert



MO

Worm and wheel set, Machined plastic (delrin)



SBF

Sealed flange bearing unit for Food Industry, cover



PGB

Accessory-holder for aluminium profile, Tool holder

Complementary products



RLX

Free running conveyor roller, PVC



RLXAC8

Free roller, Steel