

Omni-directional roller



GAL48



Mounts on a Ø8mm axle

- Multiple rollers mounted on one axle work as a conventional roller with two possible directions of movement
- The "Snap in" function allows you to securely and quickly position two omni-directional rollers together, and guarantees an optimised assembly
- Corrosion-resistant
- Suitable for dusty environments
- No maintenance required
- Materials: technopolymer and stainless steel
- Maximum conveyor speed: 0.2m/s
- Working temp range: 0°C à +40°C





Uses

- Control posts
- Assembly or handling stations

Info.

- Not sold individually, please contact us for details

Allows the load to be moved in all directions



Typical application



DISCOUNTS

Qty	1+	50+	100+	300+
Disc.	List	-20%	-30%	On request

Part number	ØD	X	Y	W	V	Max load (N)	Stock	Price each 1 to 49
GAL48-OMNI	48	3	3	21,5	40	50	✓	14.06 €

*Depending on availability - Dimensions in mm