

- Element of manual blocking

- Materials

Handle: Electrolytically stainless steel


Z6CN18.10M

Thrust washer: glass fibre reinforced

black plastic PA 6 GF 30

Hinge pin, threaded stud and washer:

polished stainless steel 303



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request



Part number	Thread	ØD	ØD1	ØD2	B	B1	H	H1	A	A1	Clamping force	Manual force	Stroke	Price each 1 to 5
											F (kN)	N	S	
LAC-M5/SS	M5	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M6/SS	M6	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M8/SS	M8	27	11	33,2	24	18,0	28,5	96,0	108,0	8	350	1,5	✓	36,06 €

*Depending on availability - Dimensions in mm

Our other products



LRR

Spring loaded latch,
Spring loaded latch



MFBSC

Stainless steel flexible
bellows coupling,
Stainless steel - with
cl...



RPB

Ballscrew bearing
unit, Support



HBM

Adjustment bushing
for half-rail guide,
Adjustment bushing



SF_ZZ

Deep groove ball
bearing, Stainless
steel



BPTR

End cap for round
tube, Standard



PR105

Articulated foot Ø103,
Ø 103



BABss

303 Stainless steel
ball pin, 303 Stainless
steel



DOMI120

Domino 120
adjustable slide, Slide




LRM2

Cylindrical bronze nut,
Bronze - 2 threads



PO

Pull handle - Multi-
sector, Tapped



BETA

Hitch pin, Hitch

Complementary products



LACT_SS

Adjustable Stainless
steel cam lever, Male