

**- Element of manual blocking**

**- Materials**

Handle: Electrolytically stainless steel


Z6CN18.10M

Thrust washer: glass fibre reinforced

black plastic PA 6 GF 30

Hinge pin, threaded stud and washer:

polished stainless steel 303



### DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-10%	On request



Part number	Thread	ØD	ØD1	ØD2	B	B1	H	H1	A	A1	Clamping force	Manual force	Stroke	Price each 1 to 5
											F (kN)	N	S	
LAC-M5/SS	M5	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M6/SS	M6	18	9	21,5	15	14,5	22,0	70,4	79,2	4	120	1,2	✓	25,99 €
LAC-M8/SS	M8	27	11	33,2	24	18,0	28,5	96,0	108,0	8	350	1,5	✓	36,06 €

\*Depending on availability - Dimensions in mm

## Our other products



RT61

Self-centering locking Assembly,  
Medium/low torque



NCT\_AT

Variable angle connector, Variable angle



PW\_PWG2

Worm - precision range, Steel




UGH32

H Type Guide units,  
For Ø32 actuators



P30

Worm and wheel gear reducer, up to 8.80 Nm



PRF\_PSA

Shaft support for aluminium profile,  
Shaft stop



DB

Steel bevel gear, 2:1



UCP\_SS

Stainless steel pillow block bearing,  
Stainless steel



GE14

Toggle latches, With padlock-holder



TBD

Manual leadscrew table with opposing



INO

Internal gear, Steel 20NCD2



BHEX

Hexagonal cap, Black technopolymer

## Complementary products



LACT\_SS

Adjustable Stainless steel cam lever, Male