

To be fitted to a Ø8mm axle



GAL48



- Multiple rollers mounted on one axle work as a conventional roller with two possible directions of movement
- The "Snap in" function allows you to securely and quickly position two omni-directional rollers together, and guarantees an optimised assembly
- Corrosion-resistant
- Suitable for dusty environments
- No maintenance required
- Materials:
technopolymer and stainless steel

Uses

- Control posts
- Assembly or handling stations

Info.

- Not sold individually, please contact us for details



Typical application

Allows the load to be moved in any direction

DISCOUNTS

Qty	1+	50+	100+	300+
Disc.	List	-20%	-30%	On request

Part number	ØD	X	Y	W	V	Max. load (daN)	Stock*	Price each 1 to 99
GAL48-OMNI	48	3	3	21,5	40	5	✓	8,14 €

*Depending on availability - Dimensions in mm

Our other products



BABtss
303 Stainless steel ball pin, 303 Stainless steel



SHA_PT
Handwheel with handle, Polyamide



CLM
Male clevis end, Stainless steel short




ZDB
Machined plastic bevel gear, 2:1



PLA
Flat magnet, Flat magnet with threaded hole



PLM-16A
Magnetic stud with threaded hole, With threaded hole



RPP5
RPP heavy duty timing belt, RPP5




BABA
Ball pin lifting ring, Steel



P20
Worm and wheel gear reducer, up to 5 Nm



GBS
Nut for ballscrew, Flanged ballscrew nut



M1
Worm and wheel set, Machined plastic (delrin)



RFK28B
Hypoid gearbox - Stainless steel, up to 130 Nm

Complementary products



RLX
Free running conveyor roller, PVC



RLXAC8
Free roller, Steel