

## Module 0,5



## Brass CuZn39Pb3



- Spur gear with JIS grade 8teeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:  
Brass CuZn39Pb3 (C6304)

### Info

- \*Torque (bending strength)



### DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-12%	On request

Part number	Teeth		ØA			Torque*		Weight	Price each				
	Z	ØP	ØD	ØM	(H7)	E	F			(Nm)	(kg)		
GB0.5-15-RA03T	15	7,5	8,5	8,5	3	3	11	14	M3	2,5	0,058	0,005	27,45 €
GB0.5-16-RA03T	16	8,0	9,0	9,0	3	3	11	14	M3	2,5	0,065	0,006	27,45 €
GB0.5-20-RA04	20	10,0	11,0	8,5	4	3	7	10	-	-	0,091	0,004	27,98 €
GB0.5-20-RA03T	20	10,0	11,0	11,0	3	3	11	14	M3	2,5	0,091	0,010	31,86 €
GB0.5-22-RA03T	22	11,0	12,0	9,0	3	3	7	10	M3	3,5	0,10	0,005	33,93 €
GB0.5-24-RA04T	24	12,0	13,0	10,0	4	3	7	10	M3	3,5	0,12	0,006	35,58 €
GB0.5-25-RA04	25	12,5	13,5	11,0	4	3	7	10	-	-	0,12	0,008	35,58 €
GB0.5-30-RA04	30	15,0	16,0	13,0	4	3	7	10	-	-	0,16	0,011	36,35 €
GB0.5-30-RA03T	30	15,0	16,0	12,0	3	3	7	10	M3	3,5	0,16	0,010	39,92 €
GB0.5-30-RA04T	30	15,0	16,0	12,0	4	3	7	10	M3	3,5	0,16	0,010	39,92 €
GB0.5-30-RA05T	30	15,0	16,0	12,0	5	3	7	10	M4	3,5	0,16	0,009	39,92 €
GB0.5-38-RA04T	38	19,0	20,0	16,0	4	3	7	10	M3	3,5	0,22	0,018	41,38 €
GB0.5-40-RA04	40	20,0	21,0	17,0	4	3	7	10	-	-	0,23	0,020	41,49 €
GB0.5-50-RA04T	50	25,0	26,0	22,0	4	3	7	10	M3	3,5	0,31	0,033	45,76 €

Dimensions in mm

Brass CuZn39Pb3



Module

0,8

- Spur gear with JIS grade Steeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:  
Brass CuZn39Pb3 (C6304)

## Info

- \*Torque (bending strength)



## DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-12%	On request

Part number	Teeth		ØP	ØD	ØM	ØA (H7)	E	F	G	ØT	J	Torque* (Nm)	Weight (kg)	Price each 1 to 5
	Z	ØP												
GB0.8-15-RA04T	15	12,0	13,6	9,0	4	4	8	12	M3	4	0,20	0,007	On request	
GB0.8-16-RA04T	16	12,8	14,4	10,0	4	4	8	12	M3	4	0,22	0,008	On request	
GB0.8-20-RA05	20	16,0	17,6	13,5	5	4	8	12	-	-	0,31	0,014	30,36 €	
GB0.8-20-RA04T	20	16,0	17,6	12,0	4	4	8	12	M3	4	0,31	0,013	On request	
GB0.8-24-RA05T	24	19,2	20,8	16,0	5	4	8	12	M4	4	0,40	0,021	37,74 €	
GB0.8-25-RA05	25	20,0	21,6	17,0	5	4	8	12	-	-	0,43	0,024	37,38 €	
GB0.8-30-RA04T	30	24,0	25,6	20,0	4	4	8	12	M3	4	0,55	0,035	45,35 €	
GB0.8-30-RA05	30	24,0	25,6	20,0	5	4	8	12	-	-	0,55	0,034	43,39 €	
GB0.8-40-RA05	40	32,0	33,6	20,0	5	4	8	12	-	-	0,79	0,046	55,17 €	

Dimensions in mm

Brass CuZn39Pb3



Module

1,0

- Spur gear with JIS grade Steeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:  
Brass CuZn39Pb3 (C6304)

**Info**

- \*Torque (bending strength)

**DISCOUNTS**

Qty	1+	6+	10+
Disc. Price	-12%	On request	On request

Part number	Teeth		ØP	ØD	ØM	ØA (H7)	E	F	G	ØT	J	Torque* (Nm)	Weight (kg)	Price each 1 to 5
	Z	ØP												
GB1-16-RA05T	16	16	18	12	5	6	8	14	M4	4	0,52	0,015	43,35 €	
GB1-18-RA06T	18	18	20	15	6	6	8	14	M4	4	0,62	0,021	44,75 €	
GB1-20-RA06T	20	20	22	16	6	6	8	14	M4	4	0,73	0,026	46,50 €	
GB1-22-RA06T	22	22	24	18	6	6	8	14	M4	4	0,83	0,033	30,20 €	
GB1-24-RA06T	24	24	26	20	6	6	8	14	M4	4	0,94	0,040	30,75 €	
GB1-30-RA06T	30	30	32	25	6	6	8	14	M4	4	1,28	0,065	63,01 €	
GB1-40-RA06T	40	40	42	28	6	6	8	14	M4	4	1,86	0,100	91,87 €	

Dimensions in mm

## Our other products



NKX

Combined bearing without inner ring, Needle and ball bearings



CLB\_T

Die cast zinc clamping lever - male, Zamak



BFDdII

Locking pin for bushes, Nickel-plated steel



PM2

Worm, Hardened steel



H3

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



PRF\_BASE

Base plate for aluminium profile, Base plate



TBD

Manual leadscrew table with opposing threads, 2kg



BOXKK

Boxed set of DIN6885A keys, Boxed set - Steel or stainless steel



AT10-50ECO

AT type timing pulley, Economy range -



PSG1HC

Skive hobbed spur gears - precision



CHTRP

Single and dual output gearboxes, Up



PR40

Articulated foot Ø50, Ø 50

## Complementary products



YG0

HEAVY DUTY spur gear, Steel 35NCD2



G0

Steel spur gear, Steel 20NCD2



ZG0

Plastic spur gear, Machined plastic (delrin)