


Module 0,5

Brass CuZn39Pb3

NEW!




- Spur gear with JIS grade 8teeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:
Brass CuZn39Pb3 (C6304)



Info

- *Torque (bending strength)



DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-12%	On request

Part number	Teeth Z	ØP	ØD	ØM	ØA (H7)	E	F	G	ØT	J	Torque* (Nm)	Weight (kg)	Price
													each 1 to 5
GB0.5-15-RA03T	15	7,5	8,5	8,5	3	3	11	14	M3	2,5	0,058	0,005	10,35 €
GB0.5-16-RA03T	16	8,0	9,0	9,0	3	3	11	14	M3	2,5	0,065	0,006	10,35 €
GB0.5-20-RA04	20	10,0	11,0	8,5	4	3	7	10	-	-	0,091	0,004	10,97 €
GB0.5-20-RA03T	20	10,0	11,0	11,0	3	3	11	14	M3	2,5	0,091	0,010	12,01 €
GB0.5-22-RA03T	22	11,0	12,0	9,0	3	3	7	10	M3	3,5	0,10	0,005	12,79 €
GB0.5-24-RA04T	24	12,0	13,0	10,0	4	3	7	10	M3	3,5	0,12	0,006	13,42 €
GB0.5-25-RA04	25	12,5	13,5	11,0	4	3	7	10	-	-	0,12	0,008	13,42 €
GB0.5-30-RA04	30	15,0	16,0	13,0	4	3	7	10	-	-	0,16	0,011	14,85 €
GB0.5-30-RA03T	30	15,0	16,0	12,0	3	3	7	10	M3	3,5	0,16	0,010	15,65 €
GB0.5-30-RA04T	30	15,0	16,0	12,0	4	3	7	10	M3	3,5	0,16	0,010	15,65 €
GB0.5-30-RA05T	30	15,0	16,0	12,0	5	3	7	10	M4	3,5	0,16	0,009	15,65 €
GB0.5-38-RA04T	38	19,0	20,0	16,0	4	3	7	10	M3	3,5	0,22	0,018	19,32 €
GB0.5-40-RA04	40	20,0	21,0	17,0	4	3	7	10	-	-	0,23	0,020	18,49 €
GB0.5-50-RA04T	50	25,0	26,0	22,0	4	3	7	10	M3	3,5	0,31	0,033	23,61 €

Dimensions in mm


Module

Brass CuZn39Pb3

0,8



NEW!



- Spur gear with JIS grade 8teeth (JISB1702-1:1998)


- Pressure angle 20°

- Material:

Brass CuZn39Pb3 (C6304)

Info

- *Torque (bending strength)



DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-12%	On request

Part number	Teeth Z	ØP	ØD	ØM	ØA (H7)	E	F	G	ØT	J	Torque* (Nm)	Weight (kg)	Price
													each 1 to 5
GB0.8-15-RA04T	15	12,0	13,6	9,0	4	4	8	12	M3	4	0,20	0,007	13,42 €
GB0.8-16-RA04T	16	12,8	14,4	10,0	4	4	8	12	M3	4	0,22	0,008	14,04 €
GB0.8-20-RA05	20	16,0	17,6	13,5	5	4	8	12	-	-	0,31	0,014	15,26 €
GB0.8-20-RA04T	20	16,0	17,6	12,0	4	4	8	12	M3	4	0,31	0,013	16,67 €
GB0.8-24-RA05T	24	19,2	20,8	16,0	5	4	8	12	M4	4	0,40	0,021	21,76 €
GB0.8-25-RA05	25	20,0	21,6	17,0	5	4	8	12	-	-	0,43	0,024	20,36 €
GB0.8-30-RA04T	30	24,0	25,6	20,0	4	4	8	12	M3	4	0,55	0,035	23,40 €
GB0.8-30-RA05	30	24,0	25,6	20,0	5	4	8	12	-	-	0,55	0,034	22,39 €
GB0.8-40-RA05	40	32,0	33,6	20,0	5	4	8	12	-	-	0,79	0,046	27,04 €

Dimensions in mm

Module


Brass CuZn39Pb3

1,0




- Spur gear with JIS grade 8teeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:
Brass CuZn39Pb3 (C6304)

NEW!



Info

- *Torque (bending strength)



DISCOUNTS

Qty	1+	6+	10+
Disc. Price	-12%	On request	

Part number	Teeth		ØA				Torque*		Weight		Price each		
	Z	ØP	ØD	ØM	(H7)	E	F	G	ØT	J	(Nm)	(kg)	1 to 5
GB1-16-RA05T	16	16	18	12	5	6	8	14	M4	4	0,52	0,015	17,71 €
GB1-18-RA06T	18	18	20	15	6	6	8	14	M4	4	0,62	0,021	19,94 €
GB1-20-RA06T	20	20	22	16	6	6	8	14	M4	4	0,73	0,026	20,72 €
GB1-22-RA06T	22	22	24	18	6	6	8	14	M4	4	0,83	0,033	22,78 €
GB1-24-RA06T	24	24	26	20	6	6	8	14	M4	4	0,94	0,040	23,19 €
GB1-30-RA06T	30	30	32	25	6	6	8	14	M4	4	1,28	0,065	28,08 €
GB1-40-RA06T	40	40	42	28	6	6	8	14	M4	4	1,86	0,100	47,40 €


Dimensions in mm

Our other products



LVTMFC

Device for controlling limit switches, For mini-actuator LVT



T5courroie

T type timing belt, T5 Steel cored polyurethane




TAC_SS

Stainless steel rigging screw (hook/eye), Stainless steel



CHT

Asynchronous AC Motor, 0.18 to 0.55kW



M0

Worm and wheel set, Bronze



BUH77

Motor-gearbox 12V and 24V DC, from 0.1 to 2 Nm



HLC19

Right angle spiro bevel gearbox, Up to 43Nm



LRR

Spring loaded latch, Spring loaded latch



KSTM

Igubal® pillow block bearing, Polymer



BPHFclip

Clip for ball transfer unit, Insert clip - Installing from above



CHM63-MOT

Asynchronous AC motorgearboxes 0.37 to 1.5kW, 0.37 to



BDMdll

Magnetic bush for pin, Fast and light magnetic locking

Complementary products