





- Standard series in accordance with DIN 808-7551
- Smooth hardened bushes
- Suitable for speeds up to 800 rpm
- Max. misalignment angle 45°
- Materials:
 - Body: C45 steel
 - Pin: Hardened steel 18NCD4



Accessories

- Optional rubber cover

Modifiable bore



Angle	Factor
5°	1,25
10°	1,00
20°	0,75
30°	0,45
40°	0,30

Effect of operating angle

The torques below are given for a 10° angle. For other angles, the appropriate factor from this table should be applied.

E.g. For 100Nm to be transmitted at 20°, the corrected value of torque becomes $100/0.75 = 133 \text{ Nm}$ and a joint should be chosen that can transmit 133Nm at the required speed.

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-6%	On request

Part number	ØD	ØA	C	M	L	Torque (Nm)								Price each	
						at 100 rpm	at 200 rpm	at 300 rpm	at 400 rpm	at 500 rpm	at 700 rpm	at 800 rpm	Stock*		
GD01-A-6/6	16	6	7,5	27	61	-	-	-	-	-	-	-	-	✓	58,04 €
GD02-A-8/8	16	8	10	27	67	-	-	-	-	-	-	-	-	✓	58,04 €
GD03-A-10/10	20	10	10	30	75	23	15	13	12	11	10	7	-	✓	60,92 €
GD04-A-12/12	22	12	11	29	74	39	23	18	15	14	12	11	-	✓	60,92 €
GD05-A-14/14	25	14	13	33	85	62	39	36	32	30	26	24	-	✓	68,25 €
GD1-A-16/16	29	16	19	35	100	78	76	65	52	46	37	32	-	✓	72,87 €
GD2-A-18/18	32	18	20	39	112	140	108	86	65	54	43	-	-	✓	87,86 €
GD3-A-20/20	40	20	19	46	128	216	151	108	86	76	54	-	-	✓	97,02 €
GD4-A-22/22	40	22	25	48	145	270	173	130	108	86	65	-	-	-	130,13 €
GD5-A-25/25	50	25	24	59	163	346	216	151	130	108	86	-	-	✓	159,05 €
GD6-A-30/30	58	30	28	66	182	389	238	173	140	119	-	-	-	-	188,96 €
GD61-A-32/32	63	32	30	84	198	-	-	-	-	-	-	-	-	-	On request
GD7-A-35/35	70	35	32	78	212	410	270	205	157	130	-	-	-	-	On request
GD8-A-40/40	80	40	38	95	245	454	302	238	194	-	-	-	-	-	On request
GD9-A-50/50	95	50	50	120	290	648	432	302	238	-	-	-	-	-	On request

*Depending on availability - Dimensions in mm

Our other products



CDPC

Flanged drill bushing,
Steel



BDM

Pin for magnetic bush,
Fast and light
magnetic locking



G-ECO

Eco range Spur gear,
Steel C45



SSB

Stainless steel bevel
gear, 1:1



SHTP

Drylin® Linear table,
Economy range



UGH16

H Type Guide units,
For Ø12 and Ø16
actuators




CNA-CNG

Right angled
mounting plate, Right
angled mounting
plate for clevis




PW_PWG2

Worm - precision
range, Steel



HLUss

Spoked handwheel,
Stainless steel 316



LAT2

2A motorised linear
actuator, 2 amperes



NSB

Standard linear
bearing housing,
Closed - Long



FF50

Offset spur gear
reducer, from 111 to
425 Nm

Complementary products



M

Bellows cover,
Accessory:



G01

Single universal joint,
Normal duty



CT

Telescopic universal
joint, Normal duty