

Spherical bushing **DIN 648**



GEc


Hard chrome/PTFE contact

- DIN 648, series E, ISO 6124/1
- Material: steel

Advantages

- No maintenance

Maintenance free



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Ød	ØD	ØD1	S	C	α	Load capacity static (N)	Load capacity dynamic (N)	Weight (g)	Stock*	Price each 1 to 5
GE6C	6 ^{+0,008}	14 ^{+0,008}	10,0	6 ^{+0,12}	4 ^{+0,24}	13°	9000	3600	4	✓	4,89 €
GE8C	8 ^{+0,008}	16 ^{+0,008}	13,0	8 ^{+0,12}	5 ^{+0,24}	15°	14600	5850	7	-	1,81 €
GE10C	10 ^{+0,008}	19 ^{+0,008}	16,0	9 ^{+0,12}	6 ^{+0,24}	12°	21600	8650	10	✓	5,38 €
GE12C	12 ^{+0,008}	22 ^{+0,008}	18,0	10 ^{+0,12}	7 ^{+0,24}	11°	28500	11400	10	✓	5,87 €
GE15C	15 ^{+0,008}	26 ^{+0,008}	22,0	12 ^{+0,12}	9 ^{+0,24}	8°	44000	17600	20	✓	7,08 €
GE17C	17 ^{+0,008}	30 ^{+0,008}	25,0	14 ^{+0,12}	10 ^{+0,24}	10°	56000	22400	30	✓	8,07 €
GE20C	20 ^{+0,010}	35 ^{+0,011}	29,0	16 ^{+0,12}	12 ^{+0,24}	9°	78000	31500	60	✓	8,58 €
GE25C	25 ^{+0,010}	42 ^{+0,011}	35,5	20 ^{+0,12}	16 ^{+0,24}	7°	127000	51000	110	✓	9,56 €
GE30C	30 ^{+0,010}	47 ^{+0,011}	40,7	22 ^{+0,12}	18 ^{+0,24}	6°	166000	65500	140	✓	11,27 €


*Depending on availability - Dimensions in mm

Our other products



SRG

Adjustable latch clamp with strike plate, Stroke from 117,4mm to 128mm



PF20NM

Worm and wheel gear reducer, up to 5 Nm



OP2

Mechanical digital position indicator, 3 numbers



PLS

Cylindrical spacer, Stainless steel 303




ZDB

Machined plastic bevel gear, 2:1



RHTplss

High Temperature Castor, up to 200kg



M0

Worm and wheel set, Machined plastic (delrin)




KK

Rounded end feather key, Steel



MFB

Flexible bellows coupling, Aluminium and Bronze - With set



H2

Crossed helical gear crossed axis at 90°, Machined plastic



BAC110

Swivel storage bin, Storage bin



CHAM5270SS

Marine hinge for welding/screw mounting, Marine

Complementary products



GE_ES

Spherical bushing, Steel / steel



GE_ES_2RS

Spherical bushing, Steel / steel with seals