

Spherical bushing **DIN 648**

GEES


Steel/steel contact

- DIN 648, series E, ISO 6124/1
- Material: steel

Info.

- Some maintenance required (except GE-E models)

Economy range



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Od	OD	OD1	S	C	δ	static (N)	dynamic (N)	Weight (g)	Stock*	Price each 1 to 5
GE6E	6 ^{-0.008}	14 ^{-0.008}	10,0	6 ^{-0.12}	4 ^{+0.24}	13°	17000	3400	<10	✓	2,92 €
GE8E	8 ^{-0.008}	16 ^{-0.008}	13,0	8 ^{-0.12}	5 ^{+0.24}	15°	27500	5500	<10	✓	2,92 €
GE10E	10 ^{-0.008}	19 ^{-0.008}	16,0	9 ^{-0.12}	6 ^{+0.24}	12°	40500	8150	10	✓	2,92 €
GE12E	12 ^{-0.008}	22 ^{-0.008}	18,0	10 ^{-0.12}	7 ^{+0.24}	11°	54000	10800	10	✓	2,92 €
GE15ES	15 ^{-0.008}	26 ^{-0.008}	22,0	12 ^{-0.12}	9 ^{+0.24}	8°	85000	17000	20	✓	2,92 €
GE17ES	17 ^{-0.008}	30 ^{-0.008}	25,0	14 ^{-0.12}	10 ^{+0.24}	10°	106000	21200	40	✓	3,16 €
GE20ES	20 ^{-0.010}	35 ^{+0.011}	29,0	16 ^{-0.12}	12 ^{+0.24}	9°	146000	30000	60	✓	3,16 €
GE25ES	25 ^{-0.010}	42 ^{+0.011}	35,5	20 ^{-0.12}	16 ^{+0.24}	7°	240000	48000	110	✓	3,66 €
GE30ES	30 ^{-0.010}	47 ^{+0.011}	40,7	22 ^{-0.12}	18 ^{+0.24}	6°	310000	62000	140	✓	4,63 €
GE35ES	35 ^{-0.012}	55 ^{+0.013}	47,0	25 ^{-0.12}	20 ^{+0.30}	6°	400000	80000	220	-	6,35 €
GE40ES	40 ^{-0.012}	62 ^{+0.015}	53,0	28 ^{-0.12}	22 ^{+0.30}	7°	500000	100000	300	✓	8,33 €
GE45ES	45 ^{-0.012}	68 ^{+0.015}	60,0	32 ^{-0.12}	25 ^{+0.30}	7°	640000	127000	400	-	9,29 €
GE50ES	50 ^{-0.012}	75 ^{+0.015}	66,0	35 ^{-0.12}	28 ^{+0.30}	6°	780000	156000	540	✓	11,76 €
GE60ES	60 ^{-0.015}	90 ^{+0.015}	80,0	44 ^{-0.15}	36 ^{+0.40}	6°	1220000	245000	1000	✓	20,62 €
GE70ES	70 ^{-0.015}	105 ^{+0.015}	92,0	49 ^{-0.15}	40 ^{+0.40}	6°	1560000	315000	1500	-	26,03 €
GE80ES	80 ^{-0.015}	120 ^{+0.015}	105,0	55 ^{-0.15}	45 ^{+0.40}	6°	2000000	400000	2200	-	38,83 €
GE90ES	90 ^{-0.020}	130 ^{+0.018}	115,0	60 ^{-0.20}	50 ^{+0.50}	5°	2450000	490000	2700	-	63,44 €
GE100ES	100 ^{-0.020}	150 ^{+0.018}	130,0	70 ^{-0.20}	55 ^{+0.50}	7°	3050000	610000	4300	-	88,04 €
GE110ES	110 ^{-0.020}	160 ^{+0.025}	140,0	70 ^{-0.20}	55 ^{+0.50}	6°	3250000	655000	4700	-	132,32 €

*Depending on availability - Dimensions in mm

Our other products




DOG319

Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



AT5-16ECO

AT type timing pulley, Economy range - AT5 aluminium



LAT4

4A motorised linear actuator, 4 amperes



HW_HT

Half-rail guide, Rail



ZG0

Plastic spur gear, Machined plastic (delrin)



SSHBRA

Stainless steel bevel gear, 1,5:1 2:1 3:1



EHD16

Internal epicyclic servo reducers, from 210 to 380 Nm




NCT

Square tube connector, Fixed angle



PT882

Drive sprocket for slat top chain, Range 882



BCM_T

Driving collar, Driving collar



UTKswc

Utilittrak® 3 wheels carriage, Series V precision steel wheel



H2

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)

Complementary products



GE_ES_2RS

Spherical bushing, Steel / steel with seals



GE_C

Spherical bushing, Hard chromium / PTFE