



## Module 1.0

Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material:  
steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1-15	15	15	17	12	6	0,08-0,16	0,02	98,74 €
GG1-16	16	16	18	13	6	0,08-0,16	0,02	101,89 €
GG1-17	17	17	19	14	6	0,08-0,16	0,02	105,11 €
GG1-18	18	18	20	15	6	0,08-0,16	0,03	107,52 €
GG1-19	19	19	21	16	6	0,08-0,16	0,03	111,50 €
GG1-20	20	20	22	17	6	0,08-0,16	0,03	112,66 €
GG1-21	21	21	23	18	8	0,08-0,16	0,04	115,85 €
GG1-22	22	22	24	18	8	0,08-0,16	0,04	117,91 €
GG1-23	23	23	25	20	8	0,08-0,16	0,04	122,25 €
GG1-24	24	24	26	20	8	0,08-0,16	0,05	125,87 €

Dimensions in mm

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG1-25	25	25	27	20	8	0,08-0,16	0,05	128,62 €
GG1-26	26	26	28	20	8	0,08-0,16	0,05	131,78 €
GG1-27	27	27	29	20	8	0,08-0,16	0,05	134,61 €
GG1-28	28	28	30	20	8	0,08-0,16	0,06	137,39 €
GG1-29	29	29	31	25	8	0,08-0,16	0,07	143,40 €
GG1-30	30	30	32	25	10	0,08-0,16	0,07	145,37 €
GG1-32	32	32	34	25	10	0,08-0,16	0,08	147,71 €
GG1-34	34	34	36	25	10	0,08-0,16	0,08	153,72 €
GG1-35	35	35	37	25	10	0,08-0,16	0,09	156,88 €
GG1-36	36	36	38	25	10	0,08-0,16	0,09	160,08 €
GG1-38	38	38	40	30	10	0,08-0,16	0,12	165,67 €
GG1-40	40	40	42	30	10	0,08-0,16	0,12	169,25 €
GG1-42	42	42	44	30	10	0,08-0,16	0,13	172,06 €
GG1-44	44	44	46	30	10	0,08-0,16	0,14	178,05 €
GG1-45	45	45	47	30	10	0,08-0,16	0,15	182,46 €
GG1-48	48	48	50	30	10	0,08-0,16	0,16	195,95 €
GG1-50	50	50	52	35	12	0,08-0,16	0,18	202,78 €
GG1-55	55	55	57	35	12	0,10-0,18	0,21	221,11 €
GG1-56	56	56	58	35	12	0,10-0,18	0,22	223,86 €
GG1-60	60	60	62	40	12	0,10-0,18	0,26	239,38 €
GG1-64	64	64	66	40	12	0,10-0,18	0,29	256,97 €
GG1-70	70	70	72	40	12	0,10-0,18	0,32	277,29 €
GG1-75	75	75	77	40	12	0,10-0,18	0,36	296,41 €
GG1-80	80	80	82	50	15	0,10-0,18	0,45	317,52 €
GG1-90	90	90	92	50	15	0,10-0,18	0,53	356,21 €
GG1-100	100	100	102	50	15	0,10-0,18	0,63	419,13 €
GG1-120	120	120	122	50	15	0,12-0,20	0,84	511,62 €

Dimensions in mm

## Our other products



CDPC  
Flanged drill bushing,  
Steel



ADL\_F  
Female eye bolt  
conforms to DIN582,  
Steel



SHN  
Hexagonal nut  
DIN934, A2 Stainless  
steel



PW\_PWG05  
Worm - precision  
range, Steel



WJUM10  
Drylin® W bearing  
block, Slide



RHTplss  
High Temperature  
Castor, up to 200kg



BLHB40  
Right angled gearbox,  
bored shafts, up to  
10.3 Nm



BFA  
Shaft locking washer,  
E clip



BLM  
Spring loaded plunger  
with ball tip, Stainless



SVT\_CH  
Screwjack - pivot  
mounting, Pivoting



ZBconique  
Machined plastic  
bevel gear, 1:1



SHW  
Plain washer, A2  
Stainless steel

## Complementary products