


## Module 3.0

## Heat treated steel



- Ground spur gear, precision JIS B1702 grade 3
- Pressure angle 20°
- Material: steel S45C
- Tooth surfaces induction hardened
- Surface hardness 48-53HRC
- Datum reference surface for teeth grinding: bore



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG3-14	14	42	48	34	16	0,10-0,20	0,51	173,28 €
GG3-15	15	45	51	36	16	0,10-0,20	0,58	176,03 €
GG3-16	16	48	54	38	16	0,10-0,20	0,66	183,24 €
GG3-17	17	51	57	37	16	0,12-0,22	0,57	189,60 €
GG3-18	18	54	60	40	16	0,12-0,22	0,80	199,94 €
GG3-19	19	57	63	45	16	0,12-0,22	0,77	212,71 €
GG3-20	20	60	66	50	20	0,12-0,22	0,98	222,33 €
GG3-21	21	63	69	52	20	0,12-0,22	0,94	236,68 €
GG3-22	22	66	72	54	20	0,12-0,22	1,20	243,40 €
GG3-23	23	69	75	56	20	0,12-0,22	1,10	257,75 €

Dimensions in mm

## DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Z Teeth	ØP PCD	ØD Outside	ØM Boss	ØA Bore	Backlash (mm)	Weight (kg)	Price each
GG3-24	24	72	78	58	20	0,12-0,22	1,40	263,31 €
GG3-25	25	75	81	60	20	0,12-0,22	1,50	275,27 €
GG3-26	26	78	84	62	20	0,12-0,22	1,50	294,86 €
GG3-27	27	81	87	65	20	0,12-0,22	1,60	300,34 €
GG3-28	28	84	90	70	20	0,12-0,22	2,00	313,94 €
GG3-29	29	87	93	70	20	0,12-0,22	1,90	322,75 €
GG3-30	30	90	96	75	25	0,12-0,22	2,20	339,88 €
GG3-32	32	96	102	75	25	0,12-0,22	2,40	368,15 €
GG3-34	34	102	108	75	25	0,14-0,24	2,40	401,64 €
GG3-35	35	105	111	80	25	0,14-0,24	2,90	408,40 €
GG3-36	36	108	114	80	25	0,14-0,24	3,00	417,56 €
GG3-38	38	114	120	80	25	0,14-0,24	3,00	449,08 €
GG3-40	40	120	126	80	25	0,14-0,24	3,50	472,98 €
GG3-42	42	126	132	80	25	0,14-0,24	3,50	506,80 €
GG3-44	44	132	138	80	25	0,14-0,24	3,80	523,56 €
GG3-45	45	135	141	80	25	0,14-0,24	4,20	546,65 €
GG3-48	48	144	150	85	25	0,14-0,24	5,30	600,93 €
GG3-50	50	150	156	85	30	0,14-0,24	5,60	620,41 €
GG3-55	55	165	171	90	30	0,14-0,24	5,90	749,91 €
GG3-56	56	168	174	90	30	0,14-0,24	6,00	756,75 €
GG3-60	60	180	186	100	30	0,14-0,24	7,40	813,71 €
GG3-70	70	210	216	100	30	0,14-0,24	9,10	1 015,39 €
GG3-75	75	225	231	100	30	0,14-0,24	10,30	1 140,48 €
GG3-80	80	240	246	100	30	0,14-0,24	11,60	1 252,90 €

Dimensions in mm

## Our other products



SH3

Parallel axis helical gear, Steel 20NCD2




MHXred

Reducing sleeve male/female, Hexagonal - stainless steel



SSHBRA

Stainless steel bevel gear, 1,5:1 2:1 3:1



SLS

Bearing block for leadscrew, Fixed Drylin® bearing block



GPLbr

Brush, brass



MSP19

Masterplate® glueable insert Ø19, Cylindrical with tapped insert



PCLA\_M

Technopolymer clamping lever - female, Plastic



LINK64

Synchronous AC Motor and- gearbox , from 1.3 to 6Nm



CHARcav

Spring hinge, to install



EPE

Wing nuts Hygienic Design®, Narrow



SSG2\_304L

Stainless steel spur gear, Stainless steel 304L



RURt

Swivel castor with central hole, Polyurethane - Aluminium rim (Free ...

Complementary products