



Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
 - Body: blackened steel
 - Rod: stainless steel
 - Buffer: steel with elastomer insert (MC25 and MC75 only)




Accessories


- See stroke end stop and universal flange

Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Effective Weight (kgme)		Max capacity (Nm)		Return spring force (N)	Rod reset time (S)	Max. side load angle	Price each 1 to 3
	Min	Max	Per cycle W3	Per hour W4				
MC25-ML	0,7	2,2	2,8	22600	3-6	0,3	2°	✓ 88,72 €
MC25-M	1,8	5,4	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC25-MH	4,6	13,6	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC75-M1	0,3	1,1	9,0	28200	4-9	0,3	2°	- 119,97 €
MC75-M2	0,9	4,8	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC75-M3	2,7	36,2	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC150-M	0,9	10,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH	8,6	86,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH2	70,0	200,0	20,0	34000	3-8	0,4	4°	- 158,92 €

*Depending on availability - Dimensions in mm

Our other products



BPHT
Ball transfer unit bolt fitting, Heavy



LSAG
Precision linear rotary ball spline, Rail - from 514 N to 15386 N



VEL
Self-gripping cable strip, electric and pneumatic cables



MSP23
Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



R_RR
Narrow spur rack, Steel



Q6
Deep groove ball bearing, Steel



HLA28
Right angle spiro bevel gearbox, Up to 182Nm



BLHT70
Right angled gearbox, from 26 to 128 Nm



SBF
Sealed flange bearing unit for Food Industry, cover



RPB
Ball screw bearing unit, Support




PRFSRAD
Dual lock for aluminium profile, Quick fitting, self



SLVVlok
Vertical toggle clamp, Vertical toggle clamp / vertical foot

Complementary products



MF
Shock Absorber -universal flange, Universal fixing



STC
Shock Absorber - stop collar, Universal flange



DZY
Cylindrical stop, Steel



DPAR_DKON
Progressive stop, Steel