



Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
 - Body: blackened steel
 - Rod: stainless steel
 - Buffer: steel with elastomer insert (MC25 and MC75 only)




Accessories


- See stroke end stop and universal flange

Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Effective Weight (kgme)		Max capacity (Nm)		Return spring force (N)	Rod reset time (S)	Max. side load angle	Price each 1 to 3
	Min	Max	Per cycle W3	Per hour W4				
MC25-ML	0,7	2,2	2,8	22600	3-6	0,3	2°	88,72 €
MC25-M	1,8	5,4	2,8	22600	3-6	0,3	2°	74,79 €
MC25-MH	4,6	13,6	2,8	22600	3-6	0,3	2°	74,79 €
MC75-M1	0,3	1,1	9,0	28200	4-9	0,3	2°	119,97 €
MC75-M2	0,9	4,8	9,0	28200	4-9	0,3	2°	119,97 €
MC75-M3	2,7	36,2	9,0	28200	4-9	0,3	2°	119,97 €
MC150-M	0,9	10,0	20,0	34000	3-8	0,4	4°	158,92 €
MC150-MH	8,6	86,0	20,0	34000	3-8	0,4	4°	158,92 €
MC150-MH2	70,0	200,0	20,0	34000	3-8	0,4	4°	158,92 €

*Depending on availability - Dimensions in mm

Our other products



HLC19

Right angle spiro bevel gearbox, Up to 43Nm



F7-I

Multifunction display, With internal sensor



CLA

Clamping lever Hygienic Usit® - female, Stainless steel



AC156-157

Strike for toggle latch, 25.5mm



PF40

Worm and wheel gear reducer, up to 18 Nm



MEF

Cylindrical sintered ferrous bush, Self-lubricating FP20 ferrous all...



PTRSS

Idler chain sprocket, For hostile environments



GGB

Female wing knob, Fully threaded



DBL821

Idler for slat top chain, Range 821



CHAsb28

Roll of hinge without pin, Plastic hinge



RCX-6

Spherical tilt washer - DIN6319, convex



LC

Friction clutch, 190 to 1800 Nm

Complementary products




RMSA

Adjustable shock-absorber, Adjustable



STC

Shock Absorber - stop collar, Universal flange



MF

Shock Absorber - universal flange, Universal fixing



DZY

Cylindrical stop, Steel