



# Self-compensating shock absorber

Not adjustable

MC

- MC25 and MC75: integrated stroke end stop and noise reducing buffer
- Working temperature 0 to +65°C
- Materials:
  - Body: blackened steel
  - Rod: stainless steel
  - Buffer: steel with elastomer insert (MC25 and MC75 only)




## Accessories


- See stroke end stop and universal flange

## Info.


- MC150: to avoid damaging the EPDM membrane **do not turn the rod**
- For better heat dissipation, do not paint shock-absorbers



MC25



MC75



MC150M

## DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Effective Weight (kgme)		Max capacity (Nm)		Return spring force (N)	Rod reset time (S)	Max. side load angle	Price each 1 to 3
	Min	Max	Per cycle W3	Per hour W4				
MC25-ML	0,7	2,2	2,8	22600	3-6	0,3	2°	✓ 88,72 €
MC25-M	1,8	5,4	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC25-MH	4,6	13,6	2,8	22600	3-6	0,3	2°	✓ 74,79 €
MC75-M1	0,3	1,1	9,0	28200	4-9	0,3	2°	- 119,97 €
MC75-M2	0,9	4,8	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC75-M3	2,7	36,2	9,0	28200	4-9	0,3	2°	✓ 119,97 €
MC150-M	0,9	10,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH	8,6	86,0	20,0	34000	3-8	0,4	4°	✓ 158,92 €
MC150-MH2	70,0	200,0	20,0	34000	3-8	0,4	4°	- 158,92 €

\*Depending on availability - Dimensions in mm

## Our other products



ES

Bipod support base,  
Plastic



HG5-ECO

Eco range Spur gear,  
Steel C45




SLBWSS

Indexing plunger,  
weldable, Weldable -  
Stainless steel



MRA

Quick link, Steel



CFC

Spring loaded position  
switch, Electric  
contact



RT61

Self-centering locking  
Assembly,  
Medium/low torque



VTLF

3 lobed handle,  
Polyamide - Brass




CHT

Asynchronous AC  
Motor, 0.55 to 1.1kW



Gdal

Double universal joint  
eco series, Low duty



M1

Wormwheel, Bronze



SFE

Female rod ends,  
Stainless steel / PTFE



SH4

Parallel axis helical  
gear, Steel 20NCD2

## Complementary products




RMSA

Adjustable shock-  
absorber, Adjustable



STC

Shock Absorber - stop  
collar, Universal  
flange



MF

Shock Absorber  
-universal flange,  
Universal fixing



DZY

Cylindrical stop, Steel