



Plastic bevel gear

Moulded nylon PA6

Ratio
1:1


- **Module 1 to 3.5**
- Moulded parts
- Material: Nylon 6 reinforced with 30% glass fibre
- Rough pilot bore after moulding

Options


- We are unable to modify these parts

Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- *Pilot bore dimension given as a guide only



ϕA :
pilot bore
requires
finishing



Economy range

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		Pilot bore no guaranteed							L	Lm	Stock*	Price each 1 to 9
	Z	Module	ØDe	ØDp	B	F	ØDn	dm	ØA*				
MEB1-16	16	1,0	17,8	16,0	14,0	4	13	18,59	5	14,0	9,0	✓	4,39 €
MEB1.5-16	16	1,5	25,0	24,0	18,0	6	20	25,10	8	17,0	8,9	✓	5,32 €
MEB1.5-20	20	1,5	32,1	30,0	20,0	8	22	28,70	6	18,0	9,0	✓	6,25 €
MEB1.5-30	30	1,5	47,1	45,0	25,0	10	35	39,70	12	22,5	12,0	✓	9,21 €
MEB2-16	16	2,0	34,8	32,0	20,0	9	25	28,80	10	17,0	9,3	✓	7,54 €
MEB2-20	20	2,0	42,8	40,0	27,0	12	32	35,70	8	22,0	12,0	✓	10,68 €
MEB2-30	30	2,0	62,8	60,0	30,0	16	50	47,80	12	27,0	12,8	✓	12,20 €
MEB2.5-16	16	2,5	43,5	40,0	27,0	10	30	37,30	12	22,0	13,3	✓	9,59 €
MEB2.5-20	20	2,5	53,5	50,0	30,0	12	38	45,90	12	27,0	16,0	✓	11,42 €
MEB2.5-30	30	2,5	78,5	75,0	35,0	18	50	59,10	14	32,0	16,0	-	16,08 €
MEB3-16	16	3,0	52,2	48,0	30,0	12	38	44,20	11	26,0	16,2	-	14,03 €
MEB3-20	20	3,0	64,2	60,0	35,0	18	44	51,10	14	31,0	13,6	✓	15,15 €
MEB3-30	30	3,0	94,2	90,0	40,0	22	60	68,10	20	36,0	19,0	✓	19,79 €
MEB3.5-20	20	3,5	74,9	70,0	40,5	22	56	58,60	58,60	36,0	19,0	-	17,57 €

*Depending on availability - Dimensions in mm

Our other products



F7-SF-SM

Multifunction display,
Right angled
mounting bracket



PW_PWG3

Worm - precision
range, Steel



P20

Worm and wheel gear
reducer, up to 5 Nm



GPB

Threaded spherical
knob, Moulded thread




CHA_GC_14SS

Stainless steel garnet
hinge, To screw



BCAss

Stainless steel splined
bush, Inox



M0

Worm and wheel set,
Machined plastic
(delrin)



DZYSS

Stainless steel
cylindrical stop,
stainless steel



SSG1

Stainless steel spur
gear, Stainless steel



DOMI30

Domino 30 adjustable
slide, Slide DOMILINE



FBL4004_K7

Brush strip per meter
PA6 fibres Ø0.3 to



BAC105

Storage bin, 8mm

Complementary products