



Plastic bevel gear

Moulded nylon 6

Ratio
1.5:1
4:1


- **Module 2 to 3**
- Moulded parts
- Material:
Nylon 6 reinforced with 30% glass fibre

Options

- We are unable to modify these parts


Info.

- The 2 bevels should form a matching pair
- Moulded pre-bore must be machined to suit the application
- *Pilot bore dimension given as a guide only




*ØA:
pilot bore
requires
finishing*

Economy range



Ratio 4:1



Ratio 1.5:1

DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Teeth		ØDe	ØDp	B	F	ØDn	ØA*	dm	L	Lm	Stock*	Price each 1 to 9
	Z	Module											
Ratio 4:1													
MFB2.5-16	16	2,5	44,9	40	30,5	18	32	15	92,6	29,0	11,7	✓	12,39 €
MFB2.5-64	64	2,5	161,2	160	35,0	18	80	20	48,8	30,0	16,0	✓	55,24 €
MFB3-16	16	3,0	53,8	48	32,0	20	35	10	108,0	30,0	11,1	✓	23,14 €
MFB3-64	64	3,0	193,5	192	42,0	20	60	19	58,8	36,0	22,0	✓	61,38 €
Ratio 1.5:1													
MHB2-20	20	2,0	43,3	40	23,0	10	30	8	43,3	23,0	10,2	-	12,54 €
MHB2-30	30	2,0	62,2	60	27,0	10	50	11	40,6	27,5	15,2	-	18,34 €

*Depending on availability - Dimensions in mm

Our other products



VQT

Quarter-turn clamp lock, Plastic or stainless steel button



M0

Worm and wheel set, Machined plastic (delrin)



HTD3M_09

HTD Heavy duty timing pulley, HTD3 Aluminium



SA_SAKH

Housing for linear bearing, Closed - light load



G-ECO

Eco range Spur gear, Steel C45



SERB

Cam latch, Cam latch



PRF_SDD_1820

Support for $\varnothing 18$ or $\varnothing 20$ mm Prox detector, $\varnothing 18$ and $\varnothing 20$



SHN

Hexagonal nut DIN934, Steel (Class 6|8|)



LSAG

Sleeve for splined ball shaft, Chariot - from 514 N to 15386 N



HTD5M_09

HTD Heavy duty timing pulley, HTD5 Aluminium



PRF_FIX_STD

Fastener for aluminium profile, Standard fastener



BLHB20

Right angled gearbox, bored shafts, up to 1.77 Nm

Complementary products