

- Stainless steel gas spring

- Materials:

Body/rod: stainless steel

Rod-end: stainless steel

- Works in compression (push) mode

- Refilling fluid: nitrogen oil

- Working temperature: -20°C to 80°C

- Operating Fluids: Nitrogen gas and oil

- Damping length (with oil)

Size 6: approx 10mm

Size 10: approx 20mm

- Filling tolerance: -20N to +40N

Important: Spring must be mounted with piston pointing down




Option

- Preset forces available to order (for orders of 5 or more):

Size 6: 10N to 400N

Size 10: 80N to 1300N



Uses

- Facilitates opening and closing of a bonnet or boot
- Saves effort



DISCOUNTS

Qty	1+	3+
Disc.	List	On request

Part number	Stroke	L	ØD1	ØD2	ØN	A	P	E	Force (N)	Price each 1 to 2
Size 6										
GSI-15-060-50	60	149	15	6	6,1	10	16	6	050	249,49 €
GSI-15-100-80	100	229	15	6	6,1	10	16	6	080	262,05 €
GSI-15-150-100	150	329	15	6	6,1	10	16	6	100	283,50 €
Size 10										
GSI-22-50-80	50	164	22	10	8,1	14	20	10	080	296,51 €
GSI-22-100-100	100	264	22	10	8,1	14	20	10	100	312,34 €
GSI-22-150-200	150	364	22	10	8,1	14	20	10	200	285,46 €
GSI-22-200-300	200	464	22	10	8,1	14	20	10	300	358,95 €
GSI-22-250-400	250	564	22	10	8,1	14	20	10	400	370,02 €

Dimensions in mm

Our other products



CAP805

Slat top chain stainless steel, Large range 805



ACL-PLAngle

Joining plate for aluminium profile, Angle connection



SLB

Indexing plunger, stainless steel



G0

Steel spur gear, Steel 20NCD2



HTD8M_50

HTD Heavy duty timing pulley, HTD8 Steel



PSP

Support profile, Panel support



NCT

Square tube connector, Fixed angle



PLM-C

Flat gripping magnet, Flat holding magnet



CHAGC-AL

Screw-in garnet hinge, Screw-on



PSPT

Flexible tube handle, PVC



MHX

Hexagonal threaded sleeve, Hexagonal - steel



AT5P_AT10P

Connecting plate for AT type timing belts, AT10

Complementary products



CLR

Straight clevis, Straight clevis for use with a male clevis



GSA_A

Adjustable gas spring, Steel



GSI_A

Gas control screw for gas spring, Gas control screw



CNA-CNG

Right angled mounting plate, Right angled mounting plate for ball jo...