

Cylindrical Master-Plate® glueable insert Ø38

MSP38

Inox 316L


- Glueable stainless steel plate with tapped insert or threaded stud
- Material:
316L stainless steel

Applications



- Industrial, transport, building, furnishings

Info.

- Glue not supplied
- Not supplied individually, contact us for details



Exemple d'application



DISCOUNTS

Qty	1+	50+	100+	500+
Disc.	List	-10%	-20%	On request

Part number	ØA	ØD	L	Form	Price each 1 to 49
MSP38EB-8-6/SS	38	M8	6,5	Blind tapped	3,11 €
MSP38E-8-6/SS	38	M8	6,5	Nut	3,11 €
MSP38F-6-40/SS	38	M6	40	Thread	3,11 €
MSP38F-8-40/SS	38	M8	40	Thread	3,51 €

Dimensions in mm

Our other products



BOX-TOR-ORFS

Box set of Nitrile O-rings NBR90Sh A, 7.65 x 1.78mm to 37.82 x 1.78



CHAu

Screwed hinge, 270°



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane




DOMI120

Accessories, Turntable



HS

Hexagonal spacer, Stainless steel 303



VKM

Square steel nut, Steel - 1 thread



PFL

P-FLEX Coupling, Set screw



TBD

Manual leadscrew table with opposing threads, 5kg



NPTR_M

Adjustable cross clamp, Adjustable



WJUM10

Drylin® W bearing block, Slide



CHTRP

Single and dual output gearboxes, Up



ABL100000

Antistatic brush, For sensitive surfaces

Complementary products



MSP3815

Masterplate® glueable insert rectangular, rectangular with

tapped i...



MSP38

Masterplate®
glueable insert Ø38,
Cylindrical Ø38 with
threaded s...



MSP23

Masterplate®
glueable insert Ø23,
Cylindrical Ø23 with
threaded s...



MSP3815

Masterplate®
glueable insert
rectangular,
rectangular with nut