

Steel spur gear



Module 5,0



C45 steel

Economy range

- Economy range of gears
- Pressure angle 20°
- Material:
C45 steel UNI7845

Info

- Pilot bore information is given as a guide only and may vary between batches
- Gear should be finished to suit the application, **we are unable to offer this service**



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-5%	On request

Part number	Z Teeth	ØP PCD	ØD External	ØM Boss	ØA Pilot bore	Stock*	Price each 1 to 3
HG5-12/ECO	12	60	70	45	16	✓	20,70 €
HG5-13/ECO	13	65	75	50	16	✓	22,76 €
HG5-14/ECO	14	70	80	55	20	✓	26,58 €
HG5-15/ECO	15	75	85	60	20	✓	27,34 €
HG5-16/ECO	16	80	90	65	20	✓	31,54 €
HG5-17/ECO	17	85	95	70	20	✓	33,67 €
HG5-18/ECO	18	90	100	70	20	✓	38,16 €
HG5-19/ECO	19	95	105	70	20	✓	41,08 €
HG5-20/ECO	20	100	110	80	20	✓	46,50 €
HG5-21/ECO	21	105	115	80	20	✓	48,61 €
HG5-22/ECO	22	110	120	80	25	✓	54,43 €
HG5-23/ECO	23	115	125	90	25	✓	57,07 €
HG5-24/ECO	24	120	130	90	25	✓	64,39 €
HG5-25/ECO	25	125	135	90	25	✓	66,31 €
HG5-26/ECO	26	130	140	100	25	✓	71,60 €
HG5-27/ECO	27	135	145	100	25	✓	75,85 €
HG5-28/ECO	28	140	150	100	25	✓	81,32 €
HG5-29/ECO	29	145	155	100	25	✓	94,19 €
HG5-30/ECO	30	150	160	100	25	✓	106,16 €

Dimensions in mm

Our other products



PRES5HR
Manual workbench press, Force up to 500kg



T39_T49
Extension spring in metre length stainless steel, by the metre



CLB_M
Die cast zinc clamping lever - female, Zamak




VDSQCB
Sliding lock adjustment system, Blocking wedge



PRF_JL6
Lip seal for panel, Door seal - Ø 6mm




SMS
Spiral bevel gear, 1:1




T0
Torsion spring, Stainless steel



PSG125
Spur gear - precision range, Case hardened steel 20NCD2



MRS
Stainless steel metric section rack, Stainless steel



ACL-PR
Joining plate for aluminium profile, Right angled




FBL6000_K19
Brush strip per meter horsehair fibres Ø0.2, Black horsehair



SCA_SS
Stainless steel flat cable clamp, Stainless steel

Complementary products



MR_MMR
Metric section rack, Steel



TRM
Spur round rack, Steel - module 1-6



HG5
Steel spur gear, Steel 20NCD2



ZHG5
Plastic spur gear, Machined plastic (delrin)