

Right angle gearbox

HLA28

Torque up to 182 Nm




- Right angle bevel gearbox
- Max speed 1,400 rpm
- Output backlash: 12' to 20'
- Materials:
 - Components: steel
 - Case: cast iron
- Thermal power: 10.3 kW (Heat dissipation capability)

Part number


- When ordering, specify the rotation direction and mounting position by replacing **E** and **B3** in the Part number (see presentation page)



With input shaft



Single output shaft S or dual shafts B



DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-5%	On request

Part number	Ratio	ØInput shaft (h6)	output shaft	Max output speed (rpm)	Mechanical output torque* (Nm)	Weight (kg)	Price each
HLA28-1-C-E-B3	1:1	28	hollow	1400	146	23	795,88 €
HLA28-2-C-E-B3	2:1	24	hollow	700	145	23	795,88 €
HLA28-3-C-E-B3	3:1	24	hollow	467	182	23	795,88 €
HLA28-1-S-E-B3	1:1	28	single	1400	146	23	713,29 €
HLA28-2-S-E-B3	2:1	24	single	700	145	23	713,29 €
HLA28-3-S-E-B3	3:1	24	single	467	182	23	713,29 €
HLA28-1-B-E-B3	1:1	28	dual	1400	146	23	757,09 €
HLA28-2-B-E-B3	2:1	24	dual	700	145	23	757,09 €
HLA28-3-B-E-B3	3:1	24	dual	467	182	23	757,09 €

*For maximum torque and a service factor applied, see presentation page - Dimensions en mm

Our other products



CHMR75

Worm and wheel gear reducer, up to 298 Nm



D-PAR_SS

Stainless steel elastomeric mount, stainless steel



DOMI50

Domino 50 adjustable slide, Slide DOMILINE 50 with counter and hand...



LRR

Catch-plate for latch, Catch-plate



METC

Flanged sintered bronze bush, Self-lubricating sintered bronze



LRM

Trapezoidal bronze nut, Bronze - 1 thread



BLHM40

Right angled gearbox, double output shafts, up to 10.3 Nm



NPCR

Adjustable cell support, Adjustable



PPG

Indexing plunger with flange, With




GLT2-17

Telescopic drawer runners for groove



ZG1

Plastic spur gear, Machined plastic



T0

Torsion spring, Stainless steel

Complementary products



HLC28

Right angle spiro bevel gearbox, Up to 182Nm



HLA24

Right angle spiro bevel gearbox, Up to 78Nm