



DryLin® N miniature guiding system

Load up to 500N

NK27
NW27

- Linear rail with polymer slide
- Reduced size (both height and surface)
- Dry working, no maintenance required
- Not affected by dust
- Corrosion-resistant
- Reduced coefficient of friction means wear is reduced
- Reduced weight thanks to use of a combination of aluminium and plastic
- Very high speeds and acceleration possible
- Replaceable sliding parts in iglidur® J
- Materials:
 - Slide body: Zinc
 - Rails: Anodised aluminium
- Symmetrical hole pattern, C5=C6



NS & NW-01




NS & NW-02

Small but effective


Options

- Rail length up to 3000mm max.


For M4 screw
DIN 7984 / DIN 6912
DIN 84 / EN ISO 1707




Type 1



Type 2



Type 1



Type 2

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK01-27-1000	1 Rail (1000mm) + 1 slide type 1	300,8	✓	61,50 €
NK02-27-1000	1 Rail (1000mm) + 1 slide type 2	302,5	✓	63,60 €
NW01-27	1 slide type 1 only	10,8	✓	4,78 €
NW02-27	1 slide type 2 only	12,5	✓	6,90 €

*Depending on availability - Dimensions in mm

Our other products



AZY

Cylindrical elasto
mount, Steel



RFK28B

Hypoid gearbox -
Stainless steel, up to
130 Nm



BH02

Single housed bearing
assembly, Bearing
secured with circlips




T5M T10M

T type timing belt per
metre, T5 Steel cored
polyurethane



DOMI120

Domino 120
adjustable slide, Slide
DOMILINE 120 with
counter and han...



M2

Worm and wheel set,
Machined plastic
(delrin)



PRF_GAL

Roller for aluminium
profile, Hollow roller
ø12



PV1R

Adjustable suction-
cup support, Standard
grip



BCM_CC

Modular cylindrical
brush, Horsehair
bristles



TPEpbd

Castor for aluminium
profile, Swivel with
brake



D19 D29

Compression springs
in metre length
stainless steel, by the



HBM

Adjustment bushing
for half-rail guide,
Adjustment bushing

Complementary products



NSKB

Drylin® Rail end cap,
Rail end cap