


Maximum loads




NK02-17




NK01-27
NK02-27



NK02-40




NK02-80



NK17
NW17


Loads up to 50N


- ***Linear rail with polymer slide unit***
- *Reduced size (both height and surface)*
- *Dry working, no maintenance required*
- *Not affected by dust*
- *Corrosion-resistant*
- *Reduced coefficient of fiction means wear is reduced*
- *Reduced weight thanks to use of a combination of aluminium and plastic*
- *Very high speeds and acceleration possible*
- *Replaceable sliding parts in iglidur® J*
- *Materials:*
  Slide unit body: Plastic
  Rails: Anodised aluminium
- *Symmetrical hole pattern, C5=C6*



Options

- *Rail length up to 1960mm max.*





For M3 screw
DIN 7984 DIN
6912 DIN 84
EN ISO 1707

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request


Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-17-1000	1 Rail (1000mm) + 1 slide unit	151,7	✔	54,75 €
NW02-17	1 slide unit only	1,7	✔	5,42 €

**Depending on availablity - Dimensions in mm*


Loads up to 500N

NK27
NW27

- ***Linear rail with polymer slide unit***
- *Reduced size (both height and surface)*
- *Dry working, no maintenance required*
- *Not affected by dust*
- *Corrosion-resistant*
- *Reduced coefficient of fiction means wear is reduced*
- *Reduced weight thanks to use of a combination of aluminium and plastic*
- *Very high speeds and acceleration possible*
- *Replaceable sliding parts in iglidur® J*
- *Materials:*
  Slide unit body: Zinc
  Rails: Anodised aluminium
- *Symmetrical hole pattern, C5=C6*



NS & NW-01




NS & NW-02


Small footprint

Options


- *Rail length up to 3000mm max.*




Type 1



Type 2



Type 1



Type 2

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK01-27-1000	1 Rail (1000mm) + 1 slide unit type 1	300,8	✔	61,28 €
NK02-27-1000	1 Rail (1000mm) + 1 slide unit type 2	302,5	✔	70,21 €
NW01-27	1 slide unit type 1 only	10,8	✔	6,88 €
NW02-27	1 slide unit type 2 only	12,5	✔	8,27 €


**Depending on availablity - Dimensions in mm*


NK40
NW40


Loads up to 700N

- ***Linear rail with polymer slide unit***
- *Reduced size (both height and surface)*
- *Dry working, no maintenance required*
- *Not affected by dust*
- *Corrosion-resistant*
- *Reduced coefficient of friction means wear is reduced*
- *Reduced weight thanks to use of a combination of aluminium and plastic*
- *Very high speeds and acceleration possible*
- *Replaceable sliding parts in iglidur® J*
- *Materials:*
  Slide unit body: Zinc
  Rails: Anodised aluminium
- *Symmetrical hole pattern, C5=C6*

Small footprint







Options

- *Rail length up to 3000mm max.*

DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-40-1000	1 Rail (1000mm) + 1 slide unit	480	✔	88,29 €
NW02-40	1 slide unit only	30	✔	13,62 €


**Depending on availablity - Dimensions in mm*

DryLin®N miniature guiding system

Loads up to 1000N

NK80
NW80


Small footprint



- ***Linear rail with polymer slide unit***
- *Reduced size (both height and surface)*
- *Dry working, no maintenance required*
- *Not affected by dust*
- *Corrosion-resistant*
- *Reduced coefficient of fiction means wear is reduced*
- *Reduced weight thanks to use of a combination of aluminium and plastic*
- *Very high speeds and acceleration possible*
- *Replaceable sliding parts in iglidur® J*
- *Materials:*
  Slide unit body: Plastic
  Rails: Anodised aluminium
- *Symmetrical hole pattern, C5=C6*

Options

- *Rail length up to 3960mm max.*



DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-6%	On request

Part number	Type	Weight (g)	Stock*	Price each 1 to 4
NK02-80-1000	1 Rail (1000mm) + 1 slide unit	1240	✔	114,66 €
NW02-80	1 slide unit only	100	✔	19,60 €

**Depending on availablity - Dimensions in mm*

Our other products



Moulded plastic bevel gear (nylon), 1.5:1



Suction cup, 2.5 bellows, nitrile



Internal gear, Machined plastic (delrin)



Marine hinge for welding/screw mounting, Marine



Spur gear coaxial gearbox, from 0.43 to 1.15 - Inline



Sealing strip, Clipsing



Right angled gearbox, from 19 to 70 Nm



Stainless/Polymer pillow block bearing, Polymer and stainless steel



Fastener for aluminium profile,



RPP heavy duty timing belt, RPP8



Adjustable latch clamp with strike



180° ball and socket joints, Steel

Complementary products



Drylin® Rail end cap, Rail end cap